

# PHILIPS

AquaTrio Pro

AquaTrio

3-in-1



FC7090/01



## Vacuums, mops and dries in one go

Save up to 50% effort. Save up to 50% time\*

AquaTrio Pro simultaneously vacuums, mops and dries, saving up to 50% time and effort\*. Fast-rotating micro-fiber brushes apply clean water to efficiently remove spills, dirt and dust in one pass - for perfect results on all hard floors\*\*.

### Easy to use and efficient

- Cleans more than 60m<sup>2</sup> with one water tank
- LED indicators to inform when action is required
- Save up to 50% energy. Save up to 70% water\*
- Self-cleaning appliance with flushing tray
- Effective with cold/warm tap water, with/without detergent
- Ideal for all hard floors\*\*

### Constant cleaning performance

- Fast rotating brushes clean themselves while in use
- Separate clean and dirty water tanks

### Revolutionary technology for perfect results


- Removes up to 99% of bacteria\*\*\* and reduces allergens
- 2 micro-fiber brushes remove all dirt, dust and grime
- Allergy friendly quality tested by ECARF
- Advanced cleaning performance for perfect results



asimpleswitch.com


# Highlights

## Cleans more than 60m<sup>2</sup>



One full tank containing 700ml cleans more than 60m<sup>2</sup> of hard floor; cleaning large areas using only a minimal amount of water.

## Fast rotating brushes



Powerful micro-fiber brushes rotate at 6700 rpm to effectively remove all spills, dust and dirt while adapting to the different shapes of the floor and even cleaning in crevices.

## Hygienic cleaning results



AquaTrio Pro removes up to 99% of all bacteria\*\*\* and reduces allergens. Because of the separation of a clean and dirty water tank all dust and allergens will be trapped in the dirty water tank.

## LED indicators

A LED indicator shows you when action is needed. It turns green when AquaTrio Pro is on and ready to clean. It turns blue when the watertanks need either to be filled up or

emptied. And finally, it turns red when there is something interfering the brushes, so you can remove the obstacle and keep cleaning easily.

## Save 50% energy/70% water\*



Highly-efficient power usage saves you up to 50% in energy consumption compared to vacuuming. You also use up to 70% less water compared to wet mopping.

## Self cleaning brushes



Brushes clean themselves during use. The centrifugal forces spin dirt and water picked up from the floor out of the brushes and into the dirty water tank. For optimal cleaning performance replace the AquaTrio Pro brushes every 6 months (FC8054).

## Self-cleaning appliance



AquaTrio Pro cleans itself. Simply place the appliance on the specially-designed flushing tray, pour a cup of tap water into it, and switch it on for a few seconds.

## Separate water tanks



Separate clean and dirty water tanks ensure that you always mop with clean water, all dirt and allergens are contained in the dirty water tank.

## Tap water



AquaTrio Pro gives excellent results using just cold or warm tap water. If required, you can also add detergent of your choice but use always a low-foaming or non-foaming floor cleaning detergent which is suitable for your hard floor.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO<sub>2</sub> emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Filtration

**Filter system:** Cyclonic. No filter to clean

## Performance

**Input power (IEC):** Max 500 W

**Mechanical power:** 6700 rpm

**Cleaning Technology:** Triple-Acceleration Technology

**Mopping element:** 2 microfiber rotating brushes

## Usability

**Surface coverage per tank:** More than 60m<sup>2</sup>

**Clean water: Refill indicator:** Yes, LED indicator

**Action radius:** 9.5 m

**Power supply:** Corded

**Start up time:** Immediately

**Suitable for wood and parquet**

**Detergents that can be used:** clear detergent or just water

**Change brush while cleaning:** Not needed

**Filters to clean:** None

**Handle for easy lifting**

**Moves forwards or backwards**

**Clean water tank capacity (max):** 0.65 L

**Dirty tank: Full indicator:** Yes, LED indicator

**Dirty water tank capacity (max):** 0.8 L

**Cord length:** 8 m

## Sustainability

**Energy efficient**

## Weight and dimensions

**Dimensions of product (LxWxH):** 305 x 320 x 1150 mm

**Weight of product:** 6.7 kg

**Weight with packaging:** 10.8 kg

**Dimensions of packaging (LxWxH):** 790 x 390 x 395 mm

## Nozzles and accessories

**Accessories included:** Flushing tray

**Nozzle width:** 320 mm

