

# PHILIPS

Vacuum cleaner  
bags

s-bag

4 x dust bags

FC8022/03



## Probably the most sold dust bag in the world

Longer performance, better filtration

s-bag<sup>®</sup> is the universal dust bag for all Philips, and Electrolux (Electrolux, AEG, Volta, Tornado) vacuum cleaners with bag. When buying replacement bags, just look for the s-bag<sup>®</sup> logo. Usage of non-original bags can damage your cleaner.

### **One standard, no hassle**

- A universal standard for an easy choice

### **Anti-allergy filtration**

- Anti-allergy, ideal for asthma and allergy sufferers
- ECARF seal of quality for trusted results

### **Top quality and hygiene**

- Hygienic closing system for easy disposal
- High resistance synthetic material, made in Sweden


# Highlights

## Universal standard



The original Philips s-bag<sup>®</sup> can be used for all Philips and Electrolux Group (Electrolux, AEG, Volta, Tornado) vacuum cleaners with bag. Skip the hassle of endlessly searching for a dust bag, simply look for the s-bag<sup>®</sup> logo.

## Anti-allergen effect



s-bag<sup>®</sup> Anti-Allergy has high filtration to capture pollen, dust particles, dust mites, mite allergens and cat allergens as small as 1 micron. This level of filtration significantly reduces exposure to allergens in your family and is of benefit to asthma and allergy sufferers.

## ECARF seal of quality



The Philips s-bag<sup>®</sup> Anti-Allergy has been awarded the ECARF seal of quality. This seal testifies towards the high levels of filtration that this vacuum bag provides. The ECARF seal of quality has been created to help allergy patients select appropriate products and services.

## Highly resistant material



The s-bag<sup>®</sup> Anti-Allergy is made of a highly resistant synthetic material, produced in Sweden.

## Hygienic closing system



The patented closing system of the Philips s-bag<sup>®</sup> allows for easy and clean disposal, without spilling the trapped dirt that is inside.

# Specifications

## Accessory specifications

Number of dust bags: 4

## Suitable for

**AirStar:** FC8220 - FC8229

**City-Line:** FC8400 - FC8439

**EasyLife:** FC8130 - FC8139

**Expression:** FC8600 - FC8629

**HomeHero:** FC8910 - FC8919

**Impact:** FC8350 - FC8399

**Jewel:** FC9050 - FC9079

**Mobilo:** FC8500 - FC8579

**Performer:** FC9150 - FC9179

**PowerLife:** FC8450 - FC8459

**SilentStar:** FC9300 - FC9319

**SmallStar:** FC8230 - FC8260

**Specialist:** FC9100 - FC9139

**Studio(Power):** FC9080 - FC9089

**Universe:** FC9000 - FC9029

**Electrolux Group:** Electrolux bag vacuum cleaners, Tornado bag vacuum cleaners, Zanussi bag vacuum cleaners

