

# PHILIPS

Vacuum cleaner  
bags


s-bag

4 x dust bags

One standard fits all

Anti-allergy filtration

FC8022/04



## s-bag<sup>®</sup> Anti-Allergy

Better filtration, ideal for allergy sufferers

s-bag<sup>®</sup> is the universal dust bag for all Philips, and Electrolux (Electrolux, AEG, Volta, Tornado) vacuum cleaners with bag. When buying replacement bags, just look for the s-bag<sup>®</sup> logo. Usage of non-original bags can damage your cleaner.

### **One standard, no hassle**

- A universal standard for an easy choice

### **Anti-allergy filtration**

- Anti-allergy, ideal for asthma and allergy sufferers

### **Top quality and hygiene**

- Hygienic closing system for easy disposal
- High resistance synthetic material, made in Sweden

# Highlights

## Universal standard



The original Philips s-bag® can be used for all Philips and Electrolux Group (Electrolux, AEG, Volta, Tornado) vacuum cleaners with bag. Skip the hassle of endlessly searching for a dust bag, simply look for the s-bag® logo.

## Anti-allergen effect



s-bag® Anti-Allergy has high filtration to capture pollen, dust particles, dust mites, mite allergens and cat allergens as small as 1 micron. This level of filtration significantly

reduces exposure to allergens in your family and is of benefit to asthma and allergy sufferers.

## Highly resistant material



The s-bag® Anti-Allergy is made of a highly resistant synthetic material, produced in Sweden.

## Hygienic closing system



The patented closing system of the Philips s-bag® allows for easy and clean disposal, without spilling the trapped dirt that is inside.

# Specifications

## Accessory specifications

Number of dust bags: 4

## Suitable for

**PowerLife:** FC8320 - FC8329, FC8450 - FC8459

**2000 Series, PowerGo:** FC8240 - FC8246, FC8293 - FC8296, FC8250, FC8253, FC8289

**3000 Series, Performer Compact:** FC8366 - FC8367, FC8370 - FC8379, FC8383 - FC8389, XD3000, XD3010, XD3030, XD3100, XD3110, XD3112, XD3140

**5000 Series, PerformerActive:** FC8563, FC8574 - FC8579, FC8584 - FC8589

**Jewel:** FC9050 - FC9079

**Performer:** FC8680 - FC8682, FC9150 - FC9179

**PerformerPro:** FC9180 - FC9199

**Performer Expert:** FC8720 - FC8728

**7000 Series, Performer Silent:** FC8741, FC8743, FC8745, FC8779 - FC8786

**Performer Ultimate:** FC8921 - FC8925, FC8941 - FC8957

