

Philips
disposable dust bag



FC8046/03

The original Philips dust bag

Philips original double layer dust bags hold more and last longer.

Does not tear easily

- Two layers of high-quality filter paper

Perfect fit

- The original Philips dust bag

PHILIPS
sense and simplicity

Specifications

General specifications

- Number of dust bags: 6
- Disposable dust bags for: FC8334 - FC8349
- Number of AFS micro filters: 2 (1 x FC833x; 1 x FC834x)
- Number of motor filters: 1



Issue date 2009-04-07

Version: 2.0.1

12 NC: 0000 000 00000

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com