

Philips EasyLife
Vacuum cleaner with bag

2000W



FC8132/01

Treat yourself to a really clean floor

Big in power, long in reach

Treat yourself to a really clean floor with the Philips EasyLife vacuum cleaner. The 2000 Watt motor of this vacuum cleaner provides high cleaning power for perfect results. Enjoy your floor more.

High cleaning power

- 2000 Watt motor generating max. 400 Watt suction power

Long reach for convenient cleaning

- Long cord for over 10m reach

Clean air in your home

- HEPA filter for excellent filtration of the exhaust air

Long lasting dust pickup

- 3 liter s-bag for long-lasting performance

Scratch-protection for parquet floors


- Parquet nozzle with soft brush hairs for scratch-protection



PHILIPS


Highlights

2000 Watt motor




This powerful 2000 Watt motor generates max. 400 Watt suction power for excellent cleaning results.

Long cord



A long cord gives you a longer reach, so that you can clean a room without having to stop. This product has over 10m reach.

HEPA filter




HEPA filter

This HEPA filter catches harmful microscopic vermin that causes respiratory allergies. To maintain

effective filtration, replace the HEPA filter every 6 months.


3 liter s-bag



3L

This large Philips dust bag capacity allows you to make optimal use of your vacuum cleaner bag, which means you have to change your dust bag less frequently.

Parquet nozzle



No more risk of scratches thanks to this nozzle with soft brush hairs, especially designed to carefully clean your hard floors.

Specifications

Design

- Color: Bright Aubergine

Filtration

- Dust bag type: s-bag
- Exhaust filter: HEPA washable filter
- Dust capacity: 3 L

Nozzles and accessories

- Accessories included: Crevice tool, Small nozzle
- Accessory storage: On tubeclip
- Additional nozzle: Parquet nozzle
- Standard nozzle: All-purpose nozzle

Performance

- Airflow (max): 42 l/s
- Input power (IEC): 1800 W
- Input power (max): 2000 W
- Noise level (Lc IEC): 80 dB
- Suction power (max): 400 W
- Vacuum (max): 28 kPa

Sustainability

- Packaging: > 90% recycled materials
- User manual: 100% recycled paper

Usability

- Carrying handle: Front
- Tube coupling: Conical
- Dust full indicator
- Power control: Electronic on appliance
- Tube type: Metal 2-piece telescopic tube
- Wheel type: Rubber
- Action radius: 10 m
- Cord length: 6 m

Weight and dimensions

- Weight of product: 5.5 kg



Issue date 2018-03-18

Version: 5.0.1

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com