

PHILIPS

Vacuum cleaner
with bag

EasyLife

2000W

FC8138/02



Treat yourself to a really clean floor

Big in power, long in reach

Treat yourself to a really clean floor with the Philips EasyLife vacuum cleaner. The 2000 Watt motor provides high cleaning power for perfect results. Enjoy your floor more.

High cleaning power

- 2000 Watt motor generating max. 400 Watt suction power

Long lasting dust pickup

- 3 liter s-bag for long-lasting performance

Clean air in your home

- HEPA filter for excellent filtration of the exhaust air

Scratch-protection for parquet floors


- Parquet nozzle with soft brush hairs for scratch-protection

Long reach for convenient cleaning

- Long cord for over 10m reach

Highlights

HEPA filter



This HEPA filter catches harmful microscopic vermin that causes respiratory allergies. To maintain effective filtration, replace the HEPA filter every 6 months.

3 liter s-bag




This large Philips dust bag capacity allows you to make optimal use of your vacuum cleaner bag, which means you have to change your dust bag less frequently.

Long cord

A long cord gives you a longer reach, so that you can clean a room without having to stop. This product has over 10m reach.

2000 Watt motor



This powerful 2000 Watt motor generates max. 400 Watt suction power for excellent cleaning results.

Design

Color: Oyster metallic

Performance

Airflow (max): 42 l/s
 Input power (IEC): 1800 W
 Input power (max): 2000 W
 Noise level (Lc IEC): 80 dB
 Suction power (max): 400 W
 Vacuum (max): 28 kPa

Filtration

Dust bag type: s-bag
 Exhaust filter: HEPA washable filter
 Dust capacity: 3 L

Usability

Tube type: Metal 2-piece telescopic tube
 Carrying handle: Front
 Dust full indicator
 Tube coupling: Conical
 Wheel type: Rubber
 Power control: Electronic on appliance
 Action radius: 10 m
 Cord length: 6 m

Nozzles and accessories

Standard nozzle: All-purpose nozzle
 Additional nozzle: Parquet nozzle
 Accessories included: Crevice tool, Small nozzle
 Accessory storage: On tubeclip

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

Weight and dimensions

Weight of product: 5.5 kg
 Dimensions of product (LxWxH): 428.5 x 314 x 213 mm

