

# PHILIPS

Bagless vacuum cleaner

EasyLife

2000W



FC8147/01



## Treat yourself to a really clean floor

### Big in power, long in reach

Treat yourself to a really clean floor with the Philips EasyLife vacuum cleaner. The 2000 Watt motor provides high cleaning power for perfect results. Enjoy your floor more.

#### High cleaning power

- 2000 Watt motor generating max. 350 Watt suction power

#### Be sure of optimum cleaning performance

- Indicator light shows when bucket needs emptying

#### Easy dust disposal

- Handle for easy removal of the dust container
- Dust container with one-button release system

#### Clean air in your home


- HEPA filter for excellent filtration of the exhaust air

#### Outstanding results on carpets and furniture

- Rotating Mini Turbo Brush for easy hair and fluff removal

# Highlights

## 2000 Watt motor



This powerful 2000 Watt motor generates max. 350 Watt suction power for excellent cleaning results.

## Indicator light




The indicator light turns on when the bucket is full and needs to be emptied. Emptying and cleaning the bucket and the filter will ensure you to keep the optimum cleaning performance.

## One-button release system



The closed dust container of the Philips bagless vacuum cleaner can be emptied by the bottom by the simple push of a button.

## HEPA filter



HEPA filter

This HEPA filter catches harmful microscopic vermin that causes respiratory allergies. To maintain effective filtration, replace the HEPA filter every 6 months.

## Mini Turbo Brush



The Mini Turbo Brush quickly removes (animal) hairs, fluff, and dust from couches, cushions, and other fabrics. This brush is ideal for pet owners.

# Specifications

## Design

Color: Dark midnight blue

## Filtration

Exhaust filter: HEPA washable filter

Filter type: HEPA

Dust capacity: 1.7 L

## Nozzles and accessories

Accessories included: Brush, Crevice tool, Small nozzle

Accessory storage: On tubeclip

Additional nozzle: Mini turbo brush

Standard nozzle: All-purpose nozzle

## Performance

Airflow (max): 38 l/s

Input power (IEC): 1800 W

Input power (max): 2000 W

Noise level (Lc IEC): 82 dB

Suction power (max): 350 W

Vacuum (max): 28 kPa

## Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

## Usability

Carrying handle: Front

Tube coupling: Conical

Dust container full indicator

Power control: Electronic on appliance

Tube type: Metal 2-piece telescopic tube

Wheel type: Rubber

Action radius: 10 m

Cord length: 6 m

## Weight and dimensions

Weight of product: 5.5 kg

