

# PHILIPS

Vacuum cleaner  
with bag

HomeCare

FC8189/01



## Your convenient cleaning partner

### Compact and easy vacuum cleaner

Thanks to its ultra-compact design, this Philips vacuum cleaner is lightweight and easy to store. The additional top handle make it convenient to lift and to carry. This is your partner for both small and big cleaning jobs.

#### **Good cleaning results**

- 1200 Watt motor generating max. 200 Watt suction power

#### **The right suction power for every surface**

- Electronic power control

#### **Easy to store**

- Small and compact
- Two parking hooks for horizontal and vertical storage

#### **Scratch protection for parquet floors**

- Soft rubber wheels


#### **No more hassle of buying dust bags**

- Permanent dust bag can easily be emptied



# Highlights

## 1200 Watt motor



This vacuum cleaner has an efficient 1200 Watt motor generating max. 200 Watt suction power for good cleaning results.

## Electronic power control



The electronic power control on the appliance makes it possible to select the right suction power for the surface you are vacuuming.

## Compact design



Thanks to its very compact design the appliance can easily be stored in small spaces and cupboards.

## Two parking hooks



With a parking hook on the rear and bottomside the appliance can be stored in different positions. The parking hook at the rear side is also very convenient for temporary parking of the tube during cleaning.

## Soft rubber wheels



This vacuum cleaner has rubber wheels making it glide smoothly over hard floors without the risk of scratches.

## Permanent dust bag



Since this cotton dust bag can easily be emptied, you will not encounter the hassle of buying dust bags anymore. It saves money and time.

## Comfortable carrying handles



This vacuum cleaner has not one, but two carrying handles. When it is on its wheels, there is a handle on top which enables you to easily move the cleaner around with very little bending. The second handle on the front side of the appliance enables you to comfortably carry it around in an upright position.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Design

**Color:** French blue

## Filtration

**Dust bag type:** Cotton bag

**Exhaust filter:** Microfilter

**Dust capacity:** 2 L

## Nozzles and accessories

**Accessories included:** Crevice tool, Small nozzle

**Accessory storage:** On board

**Standard nozzle:** All-purpose nozzle

## Performance

**Input power (max):** 1200 W

**Noise level (Lc IEC):** 82 dB

**Suction power (max):** 200 W

## Usability

**Carrying handle:** Top and front

**Tube coupling:** Conical

**Dust full indicator**

**Power control:** Electronic on appliance

**Tube type:** Plastic 3-piece tube

**Wheel type:** Rubber

**Action radius:** 8 m

**Cord length:** 5 m

