

PHILIPS

Bagless vacuum
cleaner

1200W

FC8198/01



Your convenient cleaning partner

Compact and easy vacuum cleaner

Thanks to its ultra-compact design, this Philips vacuum cleaner is lightweight and easy to store. The additional top handle makes it convenient to lift and to carry. This is your partner for both small and big cleaning jobs.

Good cleaning results

- 1200 Watt motor generating high suction power

Longer-lasting cleaning performance

- Bagless cyclonic filtration for longer lasting performance

Convenient to carry

- Two comfortable carrying handles for extra convenience

Easy to store

- Small and compact
- Two parking hooks for horizontal and vertical storage

Scratch protection for parquet floors

- Soft rubber wheels

Highlights

1200 W motor



This vacuum cleaner has an efficient 1200 Watt motor generating high suction power for good cleaning results.

Bagless cyclonic filtration



The cyclonic airflow of this filtration system makes sure the filter doesn't get clogged easily. This guarantees longer-lasting cleaning performance.

Comfortable carrying handles



This vacuum cleaner has not one, but two carrying handles. When it is on its wheels, there is a handle on top which enables you to easily move the cleaner around with very little bending. The second handle on the front side of the appliance enables you to comfortably carry it around in an upright position.

Compact design



Thanks to its very compact design the appliance can easily be stored in small spaces and cubboards.

Two parking hooks



With a parking hook on the rear and bottomside the appliance can be stored in different positions. The parking hook at the rear side is also very convenient for temporary parking of the tube during cleaning.

Soft rubber wheels



This vacuum cleaner has rubber wheels making it glide smoothly over hard floors without the risk of scratches.

Specifications

Design

Color: Chinese fire red

Filtration

Exhaust filter: Microfilter

Filter type: HEPA

Dust capacity: 1 l

Nozzles and accessories

Accessories included: Crevice tool

Accessory storage: On board

Standard nozzle: All-purpose nozzle

Performance

Input power (IEC): 1200 W

Noise level (Lc IEC): 84 dB

Suction power (max): 200 W

Usability

Carrying handle: Top and front

Tube coupling: Conical

Tube type: Plastic 3-piece tube

Wheel type: Rubber

Action radius: 8 m

Cord length: 5 m

Weight and dimensions

Dimensions of product (LxWxH): 360 x 250 x 200 mm

Weight of product: 4.4 kg