

Philips  
Vacuum cleaner with bag

HomeCare

FC8202/03



## Keep it out of sight!

Ultra-compact, with storage box

Thanks to its ultra-compact design, this vacuum cleaner is lightweight and easy to store.  
This vacuum is suitable for the s-bag.

**Easy storage of accessories in handy box**

- Plastified carton box with accessory tray

**High cleaning power**

- 1200 Watt motor generating 250 Watt suction power

**PHILIPS**  
sense and simplicity

# Specifications

## Design

- Colour: Marina blue

## Performance

- Input power (max): 1400 W
- Input power (IEC): 1200 W
- Suction power (max): 250 W
- Vacuum (max): 28 kPa
- Airflow (max): 34 l/s
- Noise level (Lc IEC): 84 dB

## Filtration

- Dust capacity: 2 l
- Dust bag type: Paper bag, s-bag
- Exhaust filter: Micro filter

## Usability

- Action radius: 9 m
- Tube type: 3-piece plastic tube
- Carrying handle: Top and front
- Dust bag full indicator
- Coupling: Conical
- Park or storage assist: Back
- Wheel type: Plastic
- Cord length: 6 m

## Nozzles and accessories

- Standard nozzle: All-purpose nozzle
- Accessories: Crevice tool
- Accessories storage: In storage box

## Dimensions and weight

- Weight: 3.5 kg

# Highlights

## Plastified carton box with accessory tray



This packaging is made of plastified carton to enhance the lifetime of usage when used for storage. It has a carton partition inside to store the hose separately from the vacuum cleaner and a carton tray to store the nozzle, tubes and accessories above the vacuum cleaner.

