

# PHILIPS

bag vacuum cleaner

All floors



FC8208/02



## Keep it out of sight!

Ultra-compact, with storage box

Thanks to its ultra-compact design, this vacuum cleaner is lightweight and easy to store. A convenient storage box neatly stores the vacuum and other cleaning accessories after use. This vacuum is also compatible with the s-bag.

### **Easy storage of accessories in handy box**

- Plastified carton box with accessory tray

### **High cleaning power**

- 1600 Watt motor generating 300 Watt max. suction power

### **Clean air in your home**

- HEPA filter for excellent filtration of the exhaust air

### **Hygienic dust bag removal**

- s-bag is the standard disposable dust bag


# Highlights

## Plastified carton box with accessory tray



This packaging is made of plastified carton to enhance the lifetime of usage when used for storage. It has a carton partition inside to store the hose separately from the vacuum cleaner and a carton tray to store the nozzle, tubes and accessories above the vacuum cleaner.

## HEPA filter



This HEPA filter catches harmful microscopic vermin that causes respiratory allergies. To maintain effective filtration, replace the HEPA filter every 6 months.

## s-bag



s-bag is the standard disposable dust bag that is widely available and easily recognizable by its logo. It is suitable for bag vacuum cleaners of Philips, Electrolux, AEG, Volta, and Tornado.

# Specifications

## Design

**Color(s):** Striking purple

**Model:** FC8208/02

## Motor

**Max. input power:** 1600 W

**IEC input power:** 1400 W

**Max. suction power:** 300 W

**Airflow:** 35 l/s

**Vacuum:** 29 kPa

## Vacuum cleaner specifications

**Exhaust filter:** HEPA washable filter (FC8029)

**Dust bag capacity:** 2 l

**Dust bag type:** S-bag

**Dust bag full indicator:**

**Cord length:** 6 m

**Action radius:** 9 m

**Tube:** 3 pieces plastic

**Coupling:** Conical

**Carrying handle:** Integrated top and front

**Park/storage assist:** Park

**Wheels:** Plastic

**Weight:** 3,5 kg

**Noise level Lc IEC:** 84 dB

## Accessories

**Accessories:** Crevice, small nozzle

**Accessory storage:** Plastified carton box

**Nozzle:** All floor