

Philips  
Vacuum cleaner with bag

HomeCare



FC8208/02



## Keep it out of sight!

Ultra-compact, with storage box

Thanks to its ultra-compact design, this vacuum cleaner is lightweight and easy to store. A convenient storage box neatly stores the vacuum and other cleaning accessories after use. This vacuum is also compatible with the s-bag.

### **Easy storage of accessories in handy box**

- Plastified carton box with accessory tray

### **High cleaning power**

- 1600 Watt motor generating 300 Watt max. suction power

### **Clean air in your home**

- HEPA filter for excellent filtration of the exhaust air

### **Hygienic dust bag removal**

- s-bag is the standard disposable dust bag

**PHILIPS**  
sense and simplicity

# Specifications

## Design

- Colour: Striking purple

## Performance

- Input power (max): 1600 W
- Input power (IEC): 1400 W
- Suction power (max): 300 W
- Vacuum (max): 29 kPa
- Airflow (max): 35 l/s
- Noise level (Lc IEC): 84 dB

## Filtration

- Dust capacity: 2 l
- Dust bag type: s-bag
- Exhaust filter: HEPA washable filter

## Usability

- Action radius: 9 m

- Tube type: 3-piece plastic tube
- Carrying handle: Top and front
- Dust bag full indicator
- Coupling: Conical
- Park or storage assist: Back
- Wheel type: Plastic
- Cord length: 6 m

## Nozzles and accessories

- Standard nozzle: All-purpose nozzle
- Accessories: Crevice tool, Small nozzle
- Accessories storage: In plastified carton storage box

## Dimensions and weight

- Weight: 3.5 kg


# Highlights

## Plastified carton box with accessory tray



This packaging is made of plastified carton to enhance the lifetime of usage when used for storage. It has a carton partition inside to store the hose separately from the vacuum cleaner and a carton tray to store the nozzle, tubes and accessories above the vacuum cleaner.

## HEPA filter



This HEPA filter catches harmful microscopic vermin that cause respiratory allergies. To maintain effective filtration, replace the HEPA filter every 6 months.

## s-bag



s-bag is the standard disposable dust bag that is widely available and easily recognisable by its logo. It is suitable for bag vacuum cleaners from Philips, Electrolux, AEG, Volta and Tornado.

