

PHILIPS

Bagged vacuum cleaner

2000 Series

900 W

99.9% dust pick-up*

Compact and lightweight

Replacement Kit



FC8245/09



High performance on all floors

With allergy filter to trap fine dust & allergens

The Philips PowerGo vacuum cleaner delivers top cleaning performance with an energy efficient motor. Keep the air in your home clean and healthy, too, thanks to our Allergy Filter that traps 99.9%+ of harmful particles.

Superior performance

- 900W motor for high suction power
- 99.9% dust pick-up* to deliver great cleaning results
- Allergy Filter captures 99.9% of particles – ECARF certified
- Multi-purpose nozzle for great cleaning on different floors

Effortless cleaning


- Compact and lightweight for easy carrying
- Long 9-meter reach goes further without unplugging
- Adjustable suction power for every cleaning task
- Onboard tool is conveniently stored so it's always to hand
- Easy long-lasting bags fit into large 3-liter dust chamber
- Replacement dust bag and filters included



asimpleswitch.com

Highlights

High-efficiency 900W motor



High-efficiency 900W motor delivers high suction power for great cleaning results.

99.9% dust pick-up*



High performance nozzle and high suction power ensure you can vacuum 99.9% of fine dust*.

Compact and lightweight



Compact and lightweight design ensure both storing and carrying the vacuum is easy.

Long 9-meter reach



9-meter reach from plug to nozzle allows longer use without unplugging.

Certified Allergy Filter



Certified allergy filter captures 99.9% of dust particles - including pollen, pet hair and dust mites - ideal for allergy sufferers.

Adjustable suction power



Choose the right level of suction for any cleaning task and every surface in your home.

Handy onboard accessories



Crevice tool is integrated into the vacuum so it's easily accessible to use any time you need.

Long-lasting 3L s-bags




Large 3-liter dust chamber and long-lasting universal bags allow optimum suction power until full, plus sealed, mess-free disposal.

Multi-purpose nozzle



Multi-purpose nozzle can be easily adjusted using the foot pedal, for optimal use on hard floors or carpets.

Extra bags and filters



4 spare dust bags and set of replacement filters included for convenience. Filters should be replaced annually.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Performance

Input power (max): 900 W
Input power (IEC): 750 W
Sound power level: 77 dB

Usability

Action radius: 9 m
Carrying handle: Top and front
Cord length: 6 m
Tube type: Metal 2-piece telescopic tube
Wheel type: Plastic
Tube coupling: Conical
Power control: Rotary knob

Design

Color: Dark Royal Blue

Filtration

Dust bag type: s-bag Classic Long
Performance
Dust capacity: 3 L
Exhaust filter: Allergy filter
Motor filter: 1 layer foam filter

Nozzles and accessories

Accessories included: 2-in-1 brush, Crevice tool
Accessory storage: On board
Extra accessories: 4 dust bags and filters
Standard nozzle: Multi-purpose nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 403 x 263 x 220 mm
Weight of product: 4.3 kg

