

# PHILIPS

Vacuum cleaner  
with bag

PowerGo

2000 W

Super Clean Air filter

3L

Turbo brush



FC8296/61

## High suction power

Removes pet hair from floors and furniture

The Philips PowerGo vacuum cleaner delivers 2000W of cleaning performance with a multipurpose nozzle for any type of floor. Keep the air in your home clean and healthy, too, thanks to our Super Clean Air filter.

### Clean air filter system

- Super Clean Air filter captures 99%+ of particles
- Easy s-bags last up to 50% longer

### Effortless cleaning

- Large 3-liter capacity means fewer bag changes
- Long 9-meter reach goes further without unplugging
- Onboard accessories are always at hand
- Adjustable suction power for every cleaning task
- Telescopic tube comfortable cleaning

### Remarkable results

- Deep-cleaning Turbo brush, perfect for pet hair
- Furniture tool removes pet hair with ease
- 2000W motor for strong suction power

# Highlights

## Deep-cleaning Turbo brush



The rotating Turbo brush nozzle sweeps away pet hair and fluff, gently opening your carpets for a deeper clean.

## Furniture tool for pet hair




The furniture tool removes hair from your pet's favorite couches, armchairs and cushions.

## Large 3-liter capacity



The large-capacity dust chamber handles a full three liters before the bag needs changing.

## Long 9-meter reach



With a reach of 9 meters from plug to nozzle, it keeps you cleaning longer without unplugging.

## Handy onboard accessories



Accessories, like a handy crevice tool, are integrated onto the vacuum so they're always at hand while you clean.

## 2000 watt motor



A powerful 2000 watt motor generates strong suction for excellent cleaning results.

## Super Clean Air filter




The Super Clean Air filter captures 99%+ of harmful particles – like pollen, dust mites or pet hair – so you can enjoy clean healthy air in your home.

## Easy, long-lasting bags




S-bags last up to 50% longer and maintain the full suction power of your vacuum cleaner right up to the moment it's full. One bag fits all models, with a sealing mechanism for tidy disposal.

## Adjustable suction power



Choose the right level of suction for any cleaning task and every surface in your home.

## Telescopic tube for comfort



A 2-piece, telescopic metal tube adjusts quickly to any height for comfortable cleaning.

# Specifications

## Performance

Input power (IEC): 1800 W  
Input power (max): 2000 W  
Sound power level: 82 dB  
Suction power (max): 350 W  
Vacuum (max): 23 kPa

## Usability

Action radius: 9 m  
Carrying handle: Top and front  
Cord length: 6 m  
Tube type: Metal 2-piece telescopic tube  
Wheel type: Plastic  
Tube coupling: Conical  
Power control: Rotary knob

## Design

Color: Dark Royal Blue

## Filtration

Dust bag type: s-bag Classic Long Performance  
Dust capacity: 3 L  
Exhaust filter: Super Clean Air filter  
Motor filter: 1 layer foam filter

## Nozzles and accessories

Accessories included: 2-in-1 brush, Crevice tool, Furniture nozzle  
Accessory storage: On board  
Additional nozzle: Turbo brush  
Standard nozzle: Multi-purpose nozzle

## Sustainability

Packaging: > 90% recycled materials  
User manual: 100% recycled paper

## Weight and dimensions

Dimensions of product (LxWxH): 403 x 263 x 220 mm  
Weight of product: 4.3 kg

