

PHILIPS

Vacuum cleaner
with bag

Performer Compact

AAA Energy Label*

Allergy filter

3L

FC8370/69



Full performance. Easy to use

Compact yet powerful with AirflowMax technology

The new Philips Performer Compact vacuum cleaner delivers top cleaning performance with minimum effort. AirflowMax technology keeps the suction power stronger for longer. The TriActive nozzle removes dust efficiently on all floors.

Remarkable cleaning results

- Revolutionary AirflowMax technology for strong suction power
- The TriActive nozzle applies 3 cleaning actions in one go
- High performance with 3AAA energy ratings

Clean air filter system

- S-bag Classic Long Performance lasts up to 50% longer
- Allergy filter captures more than 99.90% of fine dust
- ECARF allergy-friendly quality tested

Effortless cleaning

- ActiveLock couplings to easily adjust to each cleaning task
- Compact and light for effortless cleaning and easy storage
- On-board accessories for ultimate convenience



reddot award 2016
winner

Highlights

TriActive nozzle

The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

S-bag Classic Long Performance

This new Philips synthetic dust bag has been developed to provide long-lasting vacuum cleaner performance, i.e. a high level of suction power and maximum filtration, up to the moment the dust bag is full and ready for disposal.

AirflowMax technology

The unique AirflowMax technology keeps the suction power stronger for longer* to use the bag to the very end. The technology is built around the optimisation of three key elements: 1) Unique ribs profile inside the dust chamber to maximise airflow around the dustbag and enable the use of the entire bag surface. 2) Specially designed dust chamber capacity that allows the dustbag to fully unfold uniformly. 3) High quality, non-clogging fibre structures in the dustbag absorb dust without blocking the pores, which helps to avoid the reduction of suction power.

Compact and lightweight

Thanks to its small size, the appliance can be easily stored, saving valuable space. The light weight makes it easy to carry around.

On-board accessories

The vacuum cleaner is designed with integrated accessories, so that you do not need to carry extra parts around while you clean. The crevice tool is located on the canister, always ready to use.

ActiveLock couplings

The ActiveLock couplings allow you to easily connect and disconnect the different nozzles and accessories from the telescopic tube while cleaning.

Allergy filter



Developed to meet the specific needs of allergy sufferers and more generally of people demanding a higher level of hygiene.

ECARF



This vacuum cleaner is certified as Allergy friendly by the European Centre for Allergy Research Foundation. The exhaust air is purified up to 99.9% of allergens from cat and dog hairs, dust mites or pollen to support an allergy friendly home environment.

3AAA Energy rating



Engineered to achieve full performance with an A rating for energy efficiency, A rating on hard floor cleaning performance and A rating on dust re-emission.

Specifications

Performance

Annual energy consumption: 25 kW·h
 Input power (IEC): 750 W
 Sound power level: 77 dB
 Vacuum (max): 17.5 kPa

Usability

Action radius: 9 m
 Carrying handle: Front
 Cord length: 6 m
 Tube type: Metal 2-piece telescopic tube
 Wheel type: Rubber
 Tube coupling: ActiveLock

Design

Colour: Magic purple

Filtration

Dust bag type: s-bag Classic Long Performance
 Dust capacity: 3 l
 Exhaust filter: Allergy filter
 Motor filter: 1 layer foam filter

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush
 Additional nozzle: Hard floor nozzle
 Standard nozzle: TriActive nozzle

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 400 x 282 x 251 mm
 Weight of product: 4.2 kg



IF DESIGN AWARD

Award-winning products are selected by the top names in design. Each year, iF International Forum Design GmbH organises one of the world's most celebrated and valued design competitions: the iF DESIGN AWARD. Recognised as a symbol of design excellence around the world, the iF DESIGN AWARD welcomes over 5000 submissions from 70 countries every year.

