

PHILIPS

Vacuum cleaner
with bag

Performer Compact

AirflowMax technology

TriActive nozzle

Hard floors nozzle



FC8375/69



Full performance. Easy to use

Compact yet powerful with AirflowMax technology

The new Philips Performer Compact vacuum cleaner delivers top cleaning performance with minimum effort. AirflowMax technology keeps the suction power stronger for longer. The TriActive nozzle removes dust efficiently on all floors.

Remarkable cleaning results

- Revolutionary AirflowMax technology for strong suction power
- The TriActive nozzle applies 3 cleaning actions in one go

Effortless cleaning

- ActiveLock couplings to easily adjust to each cleaning task
- Compact and light for effortless cleaning and easy storage
- On-board accessories for ultimate convenience

Clean air filter system

- S-bag Classic Long Performance lasts up to 50% longer
- Allergy filter captures more than 99.90% of fine dust
- ECARF allergy-friendly quality tested

Highlights

AirflowMax technology



The unique AirflowMax technology keeps the suction power stronger for longer* to use the bag to the very end. The technology is built around the optimization of three key elements: 1) Unique ribs profile inside the dust chamber to maximize airflow around the dustbag and enable the use of the entire bag surface. 2) Specially designed dust chamber capacity that allows the dustbag to fully unfold uniformly. 3) High quality, non-clogging fibre structures in the dustbag absorb dust without blocking the pores, thus avoiding a reduction in suction power.


TriActive nozzle

The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

ActiveLock couplings

The ActiveLock couplings allow you to easily connect and disconnect the different nozzles and accessories from the telescopic tube while cleaning.

Compact and lightweight



Thanks to its small size, the appliance can be easily stored, saving valuable space. The light weight makes it easy to carry around.

On-board accessories

The vacuum cleaner is designed with integrated accessories, so that you do not need to carry extra pieces around while you clean. The crevice tool is located on the canister, always ready to use.



S-bag Classic Long Performance

This new Philips synthetic dust bag has been developed to provide long lasting vacuum cleaner performance, i.e. a high level of suction power and maximum filtration, up to the moment the dust bag is full and ready for disposal.

Allergy filter



Developed to meet the specific needs of allergy sufferers and more generally of people demanding a higher level of hygiene.

ECARF



This vacuum cleaner is certified as Allergy friendly by the European Centre for Allergy Research Foundation. The exhaust air is purified up to 99,9% of allergens from, cat & dog hairs, dust mites or pollen to support an allergy friendly home environment.

IF DESIGN AWARD

Award-winning products are selected by the top names in design. Each year, iF International Forum Design GmbH organizes one of the world's most celebrated and valued design competitions: the iF DESIGN AWARD. Recognized as a symbol of design excellence around the world, the iF DESIGN AWARD welcomes over 5,000 submissions from 70 countries every year.



RED DOT DESIGN AWARD 2016

The Red Dot Design Award is an international product design and communication design prize. Winning an award in this competition is proof that the creative minds have a vision and are able to commit, to carry out, to research and to experiment - and that they are a name to watch out for in the future. There are prize categories for product design, design agencies, and design concepts.

Specifications

Performance

Input power (IEC): 750 W
Sound power level: 81 dB
Vacuum (max): 17,5 kPa

Usability

Action radius: 9 m
Carrying handle: Front
Cord length: 6 m
Tube type: Metal 2-piece telescopic tube
Wheel type: Rubber
Tube coupling: ActiveLock

Design

Color: New blue

Filtration

Dust bag type: s-bag Classic Long
Performance
Dust capacity: 3 L
Exhaust filter: Allergy filter
Motor filter: 1 layer foam filter

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush
Additional nozzle: Hard floor nozzle
Standard nozzle: TriActive nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 400 x 282 x 251 mm
Weight of product: 4.2 kg

