

# PHILIPS

Vacuum cleaner  
with bag

Performer Compact

AAA Energy Label\*

Allergy filter

3L



FC8377/19



## Full performance. Easy to use

Compact yet powerful with AirflowMax technology

The new Philips Performer Compact vacuum cleaner delivers top cleaning performance with minimum effort. AirflowMax technology keeps the suction power stronger for longer. The TriActive nozzle removes dust efficiently on all floors.

### Remarkable cleaning results

- High performance with 3AAA energy ratings
- Revolutionary AirflowMax technology for strong suction power
- The TriActive nozzle applies 3 cleaning actions in one go

### Effortless cleaning

- Long reach tool for difficult to access areas
- On-board accessories for ultimate convenience
- ActiveLock couplings to easily adjust to each cleaning task

### Clean air filter system

- S-bag Classic Long Performance lasts up to 50% longer
- Allergy filter captures more than 99.90% of fine dust
- ECARF allergy-friendly quality tested

### 1-year supply of dust bags\*

- 5 s-bags



# Highlights

## 3AAA Energy rating



Engineered to achieve full performance with an A rating for energy efficiency, A on hard floor cleaning performance and A on dust re-emission.

## AirflowMax technology



The unique AirflowMax technology keeps the suction power stronger for longer\* to use the bag to the very end. The technology is build around the optimization of three key elements: 1) Unique ribs profile inside the dust chamber to maximize airflow around the dustbag and enable the use of the entire bag surface. 2) Specially designed dust chamber capacity that allows the dustbag to fully unfold uniformly. 3) High quality, non-clogging fibre structures in the dustbag absorb dust without blocking the pores, thus avoiding a reduction in suction power.

## TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the

dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

## Long reach tool



The Long reach tool is a clever accessory which helps you clean difficult areas like the top of the furniture or high shelves. The angle of the brush is adjustable, so you can have the exact instrument for your needs.

## On-board accessories



The vacuum cleaner is designed with integrated accessories, so that you do not need to carry extra pieces around while you clean. The crevice tool is located on the canister, always ready to use.

## ActiveLock couplings



The ActiveLock couplings allow you to easily connect and disconnect the different nozzles and accessories from the telescopic tube while cleaning.



## iF DESIGN AWARD

Award-winning products are selected by the top names in design. Each year, iF International Forum Design GmbH organizes one of the world's most celebrated and valued design competitions: the iF DESIGN AWARD. Recognized as a symbol of design excellence around the world, the iF DESIGN AWARD welcomes over 5,000 submissions from 70 countries every year.



[a simpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO<sub>2</sub> emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



reddot award 2016  
winner

## RED DOT DESIGN AWARD 2016

The Red Dot Design Award is an international product design and communication design prize. Winning an award in this competition is proof that the creative minds have a vision and are able to commit, to carry out, to research and to experiment – and that they are a name to watch out for in the future. There are prize categories for product design, design agencies, and design concepts.

# Specifications

## Performance

Energy efficiency rating: A  
Carpet cleaning class: C  
Hard floor cleaning class: A  
Dust re-emission class: A  
Input power (IEC): 750 W  
Sound power level: 78 dB  
Vacuum (max): 17,5 kPa

## Usability

Action radius: 9 m  
Carrying handle: Front  
Cord length: 6 m

Tube type: Metal 2-piece telescopic tube

Wheel type: Rubber  
Tube coupling: ActiveLock

## Design

Color: Star white

## Filtration

Dust bag type: s-bag Classic Long Performance  
Dust capacity: 3 L  
Exhaust filter: Allergy filter  
Motor filter: 1 layer foam filter

## Nozzles and accessories

Accessories included: Crevice tool, Integrated brush  
Additional nozzle: Hard floor nozzle  
Extra accessories: Long reach tool, 5 s-bags  
Standard nozzle: TriActive nozzle

## Sustainability

Packaging: > 90% recycled materials  
User manual: 100% recycled paper

## Weight and dimensions

Dimensions of product (LxWxH): 400 x 282 x 251 mm  
Weight of product: 4.2 kg

