

PHILIPS

Vacuum cleaner
with bag

CityLine

HomeCare

FC8438/02



Minimum size, maximum cleaning

A compact yet powerful 1800 W vacuum cleaner with Reach and Clean nozzle, 5-layer filtration system with Super Clean Air HEPA filter, telescopic tubes and rubber rear wheels. Ideal for smaller households or as a second vacuum cleaner.

High cleaning power

- 1800-Watt motor generating max. 340 Watts suction power

Special nozzle for hard-to-reach places

- Reach and Clean nozzle for reaching into the narrowest places

Clean air in your home

- HEPA filter for excellent filtration of the exhaust air

Easy to manoeuvre

- Weight/size/carrying handle

Hygienic dust bag removal

- s-bag is the standard disposable dust bag

Highlights

Reach and Clean nozzle



The innovative design of the Reach and Clean nozzle makes it possible to reach into the narrowest spaces simply by repositioning the nozzle head sideways, while offering 40% more suction power at the same time. And by completely reversing the nozzle, you quickly and easily convert it from use on hard floors to use on carpets and rugs.

HEPA filter



This HEPA filter catches harmful microscopic vermin that cause respiratory allergies. To maintain effective filtration, replace the HEPA filter every 6 months.

s-bag



s-bag is the standard disposable dust bag that is widely available and easily recognisable by its logo. It is suitable for bag vacuum cleaners from Philips, Electrolux, AEG, Volta and Tornado.

Specifications

Design

Colour: Pearl white

Filtration

Dust bag type: s-bag

Dust capacity: 2 l

Exhaust filter: Micro filter, Super Clean Air HEPA 12 filter

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle

Accessory storage: On tubeclip

Standard nozzle: Reach and Clean nozzle

Performance

Airflow (max): 38 l/s

Input power (IEC): 1600 W

Input power (max): 1800 W

Noise level (Lc IEC): 79 dB

Suction power (max): 340 W

Vacuum (max): 29 kPa

Usability

Action radius: 9 m

Carrying handle: Front

Cord length: 6 m

Tube coupling: Button

Dust full indicator

Power control: Electronic on appliance

Tube type: Metal lacquered 2-piece telescopic tube

Wheel type: Rubber

