

PHILIPS

Vacuum cleaner
with bag

PowerLife

1800W

350W suction power

FC8452/61



It's all about power

2000 Watt motor for great cleaning results

Great cleaning results on all floors with the Philips PowerLife vacuum cleaner thanks to its 2000 Watt motor.

High cleaning power

- 2000 Watt motor generating max. 350 Watt suction power

Long lasting dust pickup

- 3 liter s-bag for long-lasting performance

Ergonomic grip for far reach

- Reach all corners thanks to the extra long ergonomic grip

Lightweight metal telescopic tube

- Comfortable cleaning thanks to the lightweight aluminum tube

Highlights

2000 Watt motor



This powerful 2000 Watt motor generates max. 350 Watt suction power for excellent cleaning results.

3 liter s-bag



This large Philips dust bag capacity allows you to make optimal use of your vacuum cleaner bag, which means you have to change your dust bag less frequently.

Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

Aluminum telescopic tube



The lightweight, aluminum vacuum cleaner tube is comfortable to use and carry. The 2-piece telescopic tube can be easily adjusted to your preferred height.

Specifications

Design

Color: Deep black

Filtration

Dust bag type: s-bag
Exhaust filter: Microfilter
Dust capacity: 3 L

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle

Accessory storage: On tubeclip

Standard nozzle: All-purpose nozzle

Performance

Airflow (max): 41 l/s
Input power (IEC): 1800 W
Input power (max): 2000 W
Noise level (Lc IEC): 83 dB
Suction power (max): 350 W
Vacuum (max): 27 kPa

Usability

Carrying handle: Front
Tube coupling: Conical
Dust full indicator
Handgrip: Extra long ergonomic grip
Power control: Electronic on appliance
Tube type: Aluminum telescopic tube
Wheel type: Plastic
Action radius: 9 m
Cord length: 6 m

Weight and dimensions

Dimensions of product (LxWxH): 406 x 282 x 220 mm
Weight of product: 4.2 kg

