

# PHILIPS

Vacuum cleaner  
with bag

PowerLife

TriActive+ nozzle

FC8457/69



## Full performance

### Less energy consumption

Great cleaning results on all floors with the Philips PowerLife vacuum cleaner thanks to the unique TriActive+ nozzle.

#### **Excellent cleaning results**

- New 3-in-1 TriActive+ nozzle picks up coarse and fine dust

#### **Ergonomic grip for far reach**

- Reach all corners thanks to the extra long ergonomic grip

#### **Lightweight metal telescopic tube**

- Comfortable cleaning thanks to the lightweight aluminum tube

#### **Long lasting dust pickup**

- 3 liter s-bag for long-lasting performance



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## 3 liter s-bag



This large Philips dust bag capacity allows you to make optimal use of your vacuum cleaner bag, which means you have to change your dust bag less frequently.

## Aluminum telescopic tube



The lightweight, aluminum vacuum cleaner tube is comfortable to use and carry. The 2-piece telescopic tube can be easily adjusted to your preferred height.

## TriActive+ nozzle



The TriActive+ nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It sweeps up the dust and dirt alongside furniture and walls with its two side brushes.

## Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

# Specifications

## Performance

Airflow (max): 29,4 l/s l/s  
Annual energy consumption: 33.7 kW·h  
Input power (IEC): 750 W  
Sound power level: 84 dB  
Vacuum (max): 19,5 kPa

## Usability

Action radius: 8 m  
Carrying handle: Front  
Cord length: 5 m  
Tube type: Aluminum telescopic tube  
Wheel type: Plastic  
Tube coupling: Conical  
Power control: Electronic on appliance

## Design

Color: Deep black and green

## Filtration

Dust bag type: s-bag Classic Long Performance  
Dust capacity: 3 L  
Exhaust filter: Microfilter

## Nozzles and accessories

Accessories included: Crevice tool, Small nozzle  
Accessory storage: On tubeclip  
Standard nozzle: TriActive+ nozzle

## Sustainability

Packaging: > 90% recycled materials  
User manual: 100% recycled paper

## Weight and dimensions

Dimensions of product (LxWxH): 406 x 282 x 220 mm  
Weight of product: 4.2 kg



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.