

# PHILIPS

Bagless vacuum  
cleaner

PowerPro Compact

1800W

PowerCyclone 4

HEPA 10 washable filter

Parquet

FC8473/61



## 20% higher suction power\* for a better clean

### With PowerCyclone 4 Technology

The new Philips PowerPro Compact vacuum cleaner delivers powerful performance without compromises thanks to the PowerCyclone 4 technology and advanced bucket design

#### Clean air in your home

- The EPA filter catches microscopic vermin causing allergy

#### Scratch-protection for parquet floors

- Parquet nozzle with soft brush hairs for scratch-protection

#### Ergonomic grip for far reach

- Reach all corners thanks to the extra long ergonomic grip

#### Powerful cleaning performance

- 1800 Watt motor for high performance
- PowerCyclone 4 technology separates dust and air in one go

#### Easy to clean

- Advanced dust container design for easy to emptying

# Highlights

## Parquet nozzle



No more risk of scratches thanks to this nozzle with soft brush hairs, especially designed to carefully clean your hard floors.

## 1800 Watt Motor



The 1800 Watt motor generates max 350 Watt suction power for high performance.

## Easy to empty dust container



The dust container is perfectly designed to dispose dust without creating a dust cloud. Thanks to its unique shape and smooth surface, dust is collected at one side of the container and evenly glides into the dust bin.

## PowerCyclone 4 Technology




PowerCyclone 4 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber to separate the dust from the air.

## EPA filter system



The pleated EPA filter has a large filter surface and good filtration performance. In combination with the cyclonic airflow, this prevents it from clogging fast and gives you better and longer-lasting filtration results.

## Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

# Specifications

## Design

**Color:** Deep black

## Performance

**Input power (max):** 1800 W

**Input power (IEC):** 1600 W

**Suction power (max):** 350 W

**Vacuum (max):** 25 kPa

**Airflow (max):** 35 l/s

**Noise level (Lc IEC):** 83 dB

## Filtration

**Dust capacity:** 1.5 L

**Exhaust filter:** Sponge

**Motor filter:** EPA 10 washable filter

## Usability

**Action radius:** 9 m

**Cord length:** 6 m

**Tube type:** Metal 2-piece telescopic tube

**Carrying handle:** Front

**Tube coupling:** Conical

**Wheel type:** Plastic

## Nozzles and accessories

**Standard nozzle:** All-purpose nozzle

**Additional nozzle:** Parquet nozzle

**Accessories included:** Crevice tool, Small nozzle

## Sustainability

**Packaging:** > 90% recycled materials

**User manual:** 100% recycled paper

## Weight and dimensions

**Weight of product:** 4.5 kg

**Dimensions of product (LxWxH):**

406x285x238 mm