

Bagless vacuum  
cleaner

PowerPro Compact


Energy efficiency class B

PowerCyclone 4

TriActive+ nozzle

EPA 10 washable filter

FC8477/69



## Full performance

### Less energy consumption

The new Philips PowerPro Compact vacuum cleaner delivers powerful performance without compromises thanks to the PowerCyclone 4 technology and advanced bucket design.

#### **Clean air in your home**

- The EPA filter catches microscopic dust mites, which can cause allergies

#### **Excellent cleaning results**

- New 3-in-1 TriActive+ nozzle picks up coarse and fine dust
- PowerCyclone 4 technology separates dust and air in one go
- Energy efficiency class B

#### **Ergonomic grip for a long reach**

- Reach all corners thanks to the extra-long ergonomic grip

#### **Easy to clean**

- Advanced dust container design for hygienic emptying

# Highlights

## Easy to empty dust container



The dust container is carefully designed for disposing of collected dirt without creating a dust cloud. It is one-hand operated and, thanks to its unique shape and smooth surface, you can easily control the emptying of the dust container.

## TriActive+ nozzle



The TriActive+ nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up bigger bits of dirt with its larger opening at the front. 3) It sweeps up the dust and dirt alongside furniture and walls with its two side brushes.

## PowerCyclone 4 Technology



PowerCyclone 4 technology maximises airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight


and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber to separate the dust from the air.

## Extra-long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra-long design gives you further reach, so you can easily clean hard-to-reach places.

## Energy efficiency class B



This vacuum cleaner is engineered to achieve full performance with an energy efficiency class B.

## EPA filter system



The pleated EPA filter has a large surface and good filtration performance. In combination with the cyclonic airflow, this prevents it from clogging up quickly and gives you better and longer-lasting filtration results.

# Specifications

## Performance

**Energy efficiency rating:** B  
**Annual energy consumption:** 33.8 kW·h  
**Carpet cleaning class:** E  
**Hard floor cleaning class:** E  
**Dust re-emission class:** C  
**Sound power level:** 79 dB  
**Input power (IEC):** 750 W  
**Airflow (max):** 28.4 l/s  
**Vacuum (max):** 17.4 kPa

## Design

**Colour:** Deep black and green

## Filtration

**Dust capacity:** 1.5 l  
**Exhaust filter:** Micro filter  
**Motor filter:** EPA 10 washable filter

## Usability

**Action radius:** 8 m  
**Cord length:** 5 m  
**Tube type:** Metal 2-piece telescopic tube  
**Carrying handle:** Front  
**Tube coupling:** Conical  
**Wheel type:** Plastic

## Nozzles and accessories

**Standard nozzle:** TriActive+ nozzle  
**Accessories included:** Crevice tool, Small nozzle  
**Accessory storage:** On tubeclip

## Weight and dimensions

**Weight of product:** 4.5 kg  
**Dimensions of product (LxWxH):** 406 x 285 x 238 mm

## Sustainability

**Packaging:** > 90% recycled materials  
**User manual:** 100% recycled paper