

# PHILIPS

Bagless vacuum  
cleaner

PowerPro Compact

PowerCyclone 4

TriActive nozzle

EPA 10 washable filter

FC8477/91



## Full performance

### Less energy consumption

The new Philips PowerPro Compact vacuum cleaner delivers powerful performance without compromises thanks to the PowerCyclone 4 technology and advanced bucket design.

#### Excellent cleaning results

- PowerCyclone 4 technology separates dust and air in one go
- The TriActive nozzle applies 3 cleaning actions in one go

#### Easy to clean

- Advanced dust container design for hygienic emptying

#### Ergonomic grip for far reach

- Reach all corners thanks to the extra long ergonomic grip

#### Clean air in your home

- The EPA filter catches microscopic vermin causing allergy

# Highlights

## PowerCyclone 4 Technology



PowerCyclone 4 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber to separate the dust from the air.

## Easy to empty dust container



The dust container is carefully designed to dispose collected dirt without creating a dust cloud. It is one-hand operated and thanks to its unique shape and smooth surface, you can easily control the emptying of the dust container.

## Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

## EPA filter system



The pleated EPA filter has a large filter surface and good filtration performance. In combination with the cyclonic airflow, this prevents it from clogging fast and gives you better and longer-lasting filtration results.

## TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

# Specifications

## Performance

Annual energy consumption: 33.8 kW-h  
 Sound power level: 79 dB  
 Input power (IEC): 750 W  
 Airflow (max): 28,4 l/s  
 Vacuum (max): 17,4 kPa

## Design

Color: Deep black and green

## Filtration

Dust capacity: 1.5 L  
 Exhaust filter: Sponge  
 Motor filter: EPA 10 washable filter

## Usability

Action radius: 8 m  
 Cord length: 5 m  
 Tube type: Metal 2-piece telescopic tube  
 Tube coupling: Conical  
 Wheel type: Plastic  
 Carrying handle: Front

## Nozzles and accessories

Standard nozzle: TriActive nozzle  
 Accessories included: Crevice tool, Small nozzle  
 Additional nozzle: Hard floor nozzle

## Weight and dimensions

Weight of product: 4.5 kg  
 Dimensions of product (LxWxH): 406 x 285 x 238 mm

## Sustainability

Packaging: > 90% recycled materials  
 User manual: 100% recycled paper

