

PHILIPS

Vacuum cleaner
with bag

Performer Active

99.9% dust pick-up

900W

TriActive+ nozzle

FC8577/19



Full performance. For a deep clean.

Hygienic cleaning with AirflowMax

The new Philips Performer Active vacuum cleaner delivers full cleaning performance with hygienic dust removal. AirflowMax technology keeps the suction power stronger for longer*. The TriActive+ nozzle removes dust efficiently on all floors.

Remarkable cleaning results

- High performance with 3AAA energy ratings
- New 3-in-1 TriActive+ nozzle picks up coarse and fine dust
- Revolutionary AirflowMax technology for strong suction power

Maximum convenience

- 4L dust capacity for longer cleaning
- ActiveLock couplings to easily adjust to each cleaning task
- Integrated brush for ultimate convenience
- Soft bumper for easy gliding along furniture and walls

Hygienic cleaning

- Allergy filter captures more than 99.90% of fine dust
- ECARF allergy-friendly quality tested
- s-bag Classic Long Performance lasts up to 50% longer

Remarkable results

- 99.9% dust pick-up* to deliver high cleaning



Highlights

3AAA Energy rating



Engineered to achieve full performance with an A rating for energy efficiency, A on hard floor cleaning performance and A on dust re-emission.

TriActive+ nozzle



The TriActive+ nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It sweeps up the dust and dirt alongside furniture and walls with its two side brushes.

AirflowMax technology



The unique AirflowMax technology keeps the suction power stronger for longer* to use the bag to the very end. The technology is built around the optimization of three key elements: 1) Unique ribs profile inside the dust chamber to maximize airflow around the dustbag and enable the use of the entire bag surface. 2)

Specially designed dust chamber capacity that allows the dustbag to fully unfold uniformly. 3) High quality, non-clogging fibre structures in the dustbag absorb dust without blocking the pores, thus avoiding a reduction in suction power.

4L dust capacity



The specially designed 4L dust chamber allows you to make optimal use of your dust bag, so you can clean for longer.

ActiveLock couplings



The ActiveLock couplings allow you to easily connect and disconnect the different nozzles and accessories from the telescopic tube while cleaning.

Integrated Brush



The vacuum cleaner is designed with integrated accessories, so that you do not need to carry extra pieces around while you

clean. The soft dusting brush is conveniently integrated in the handle of the appliance, always ready to use.

Soft bumper



The soft bumper protects furniture and prevents damage if you accidentally bump into your furniture or walls and stops it from getting stuck on edges, so you can move around faster.

Allergy filter



Developed to meet the specific needs of allergy sufferers and more generally of people demanding a higher level of hygiene.



5 years warranty

Register at philips.com/welcome within 3 months of purchase to enjoy 5-year warranty on the motor for free!

Specifications

Performance

Input power (max): 900 W
Hard floor cleaning class: A
Airflow (max): 32,17 l/s
Input power (IEC): 650 W
Sound power level: 77 dB
Annual energy consumption: 27 kW·h
Vacuum (max): 17,5 kPa

Usability

Action radius: 9 m
Carrying handle: Front
Cord length: 6 m
Tube type: Metal 2-piece telescopic tube

Wheel type: Rubber
Tube coupling: ActiveLock
Power control: Rotary knob

Design

Color: Copper Grey

Filtration

Dust bag type: s-bag Classic Long Performance
Dust capacity: 4 L
Exhaust filter: Allergy filter
Motor filter: Microfilter

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush
Additional nozzle: Hard floor nozzle
Standard nozzle: TriActive+ nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH):
447x304x234 mm
Weight of product: 5,2 kg

