

Bagged vacuum cleaner

5000 series

99.9% dust pick-up

900 W

4L

Turbo brush



FC8578/09



Most powerful bagged vacuum cleaner by Philips

Locks >99.9%* of dust with 50% longer bag usage**

The Philips Performer vacuum cleaner delivers top cleaning performance with low energy consumption. Keep the air in your home clean and healthy too thanks to our Allergy Filter, which traps 99.9%+ of harmful particles.

Superior performance

- Revolutionary AirflowMax technology for strong suction power
- 900 W motor for high suction power
- 99.9% dust pick-up* to deliver deep cleaning results
- Allergy Filter captures 99.9% of particles — ECARF certified
- TriActive+ nozzle to deliver high performance on all floors
- Turbo brush, perfect for (pet) hair and fluff cleaning

Effortless cleaning

- Soft brush integrated into handle, always ready to use
- Easy long-lasting bags fit into large 4 litre dust chamber
- ActiveLock couplings easily adjust to every task



Highlights

AirflowMax technology



Uniquely designed dust chamber maximises capacity and airflow with a non-clogging dust bag, which enables strong suction power right up until the dust bag is full.

High-efficiency 900 W motor



High-efficiency 900 W motor delivers high suction power for deep cleaning results.

99.9% dust pick-up*



TriActive+ nozzle and high suction power ensure that you can vacuum 99.9% of fine dust*.

Certified Allergy Filter



Certified allergy filter captures 99.9% of dust particles - including pollen, pet hair and dust mites - ideal for allergy sufferers.

Integrated brush



Dusting brush tool is built into the handle so it's always ready to use on furniture, flat surfaces and upholstery.

Long-lasting 4 L S-bags



Large 4 litre dust chamber and long-lasting universal bags allow optimum suction power until full, plus sealed, mess-free disposal.

TriActive+ nozzle



TriActive+ nozzle utilises 3 cleaning actions in one go. It features a larger opening at the front to suck up larger debris while the specially designed soleplate removes dust from deep within carpets. Air channels on both sides of the nozzle pick up any dust and dirt alongside walls or furniture.

ActiveLock couplings



ActiveLock couplings allow attachments to easily fit to the telescopic tube with a simple snap.

Turbo brush



The rotating Turbo brush is designed for optimal cleaning of pet hair and fluff, opening up carpet fibres for a deeper clean.



5-year warranty

Register at philips.com/welcome within 3 months of purchase to enjoy 5-year warranty on the motor for free!



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO₂ emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Performance

Input power (max): 900 W

Airflow (max): 32.17 l/s

Input power (IEC): 650 W

Sound power level: 77 dB

Vacuum (max): 17.5 kPa

Usability

Action radius: 9 m

Carrying handle: Front

Cord length: 6 m

Tube type: Metal 2-piece telescopic tube

Wheel type: Rubber

Tube coupling: ActiveLock

Power control: Rotary knob

Design

Colour: Deep Black

Filtration

Dust bag type: s-bag Classic Long

Performance

Dust capacity: 4 l

Exhaust filter: Allergy filter

Motor filter: Micro filter

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush

Additional nozzle: Hard floor nozzle, Turbo brush

Standard nozzle: TriActive+ nozzle

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 447 x 304 x 234 mm

Weight of product: 5.2 kg

