



Philips Expression
Vacuum cleaner with bag

HomeCare



FC8602/01

Highest cleaning power for your money

This powerful 1800 W vacuum cleaner provides no less than 350 W of suction power! This model comes with an extra parquet nozzle and rubber wheels, and has a 5-layer filtration system, Clean Comfort Cassette and extra-long cord.

High cleaning power

- 1800 Watt motor generating max. 350 Watt suction power

Hygienic disposal of dust bag

- Unique Clean Comfort Cassette to avoid contact with dust

PHILIPS
sense and simplicity

Specifications

Design

- Colour: Deep red

Filtration

- Dust bag type: s-bag
- Dust capacity: 3 l
- Exhaust filter: Super Clean Air HEPA 12 filter

Nozzles and accessories

- Accessories: Crevice tool, Small nozzle
- Accessory storage: On tubeclip
- Standard nozzle: Wheeled all-purpose nozzle

Performance

- Airflow (max): 40 l/s

- Input power (IEC): 1600 W
- Input power (max): 1800 W
- Noise level (Lc IEC): 82 dB
- Suction power (max): 350 W
- Vacuum (max): 30 kPa

Usability

- Action radius: 10 m
- Clean Comfort cassette
- Cord length: 7 m
- Tube coupling: Conical
- Dust bag full indicator
- Power control: Electronic on appliance
- Tube type: Metal lacquered 2-piece telescopic tube
- Wheel type: Plastic

Highlights

Clean Comfort Cassette



When disposing of the dust bag, there will be no contact with the dust thanks to this patented dust bag holder.

