

# PHILIPS

Vacuum cleaner  
with bag

Performer Active

2100 W

AirflowMax technology

EPA 10 filter

Animal+

FC8657/61



## Maximum suction power for better cleaning results\*

With AirFlow Max technology and 4L dust capacity

The new Philips Performer Active delivers a better clean thanks to the Airflow Plus technology and the Powerful 2100W motor

### Excellent cleaning results

- Revolutionary Airflow Max technology for extreme suction
- 2000 W motor generates max. 425 suction power
- 4L dust capacity for longer cleaning

### Convenience

- Reach all corners thanks to the extra long ergonomic grip

### Integrated Anti-Allergy system

- EPA AirSeal with EPA 10 filter for a healthy air
- S-bag Classic Long Performance lasts up to 50% longer

### Outstanding results on carpets and furniture

- Turbo Brush nozzle removes 25% more hairs and dust

# Highlights

## Airflow Max technology



Airflow Max technology maximizes the airflow, allowing the dustbag to unfold uniformly, so you get the highest suction power, even as the bag fills-up!


## 2000 Watt motor

2000 W motor generates max. 425 suction power for excellent cleaning results.

## 4L dust capacity

The specially designed 4L dust chamber allows you to make optimal use of your dust bag, so you can clean for longer.

## Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

## EPA 10 AirSeal

EPA 10 Filter and AirSeal capture the finest dust before the air is blown out for a dust-free environment and clean, healthy air.

## S-bag Classic Long Performance

This new Philips synthetic dust bag has been developed to provide long lasting vacuum cleaner performance, i.e. a high level of suction power and maximum filtration, up to the moment the dust bag is full and ready for disposal.

## Turbo Brush nozzle



The Turbo Brush nozzle allows deep cleaning of carpets and quick hair and fluff removal from carpets. The rotating brush actively removes small dust particles and hairs, resulting in a 25% better cleaning performance on carpets. The wheels of the nozzle prevent damage in case of use on hard-floors.

# Specifications

## Design

Color: Sparkle Black

## Performance

Airflow (max): 47 l/s  
Input power (IEC): 1800 W  
Input power (max): 2100 W  
Sound power level: 80 dB  
Suction power (max): 425 W  
Vacuum (max): 34 kPa

## Filtration

Exhaust filter: EPA 10 filter  
Motor filter: Microfilter  
Dust capacity: 4 L

## Usability

Tube type: Metal 2-piece telescopic tube  
Carrying handle: Front  
Tube coupling: Conical  
Wheel type: Rubber  
Action radius: 9 m  
Cord length: 6 m

## Nozzles and accessories

Standard nozzle: Multi-purpose nozzle  
Additional nozzle: Turbo brush  
Accessories included: Crevice tool, Small nozzle

## Sustainability

User manual: 100% recycled paper

## Weight and dimensions

Weight of product: 5.2 kg  
Dimensions of product (LxWxH):  
447x304x234 mm

