

PHILIPS

Bagless vacuum cleaner

PowerPro Active

2000 W

PowerCyclone 4

Multi Clean nozzle

EPA 10 filter



FC8670/71

High suction power with PowerCyclone 4 Quick and easy emptying

The new Philips PowerPro Active bagless vacuum cleaner delivers high cleaning performance, thanks to PowerCyclone technology and Multi Clean nozzle, engineered to maximize dust pick-up. The dust container is easy to empty, with no dust cloud

Remarkable cleaning results

- PowerCyclone 4 technology separates dust and air in one go
- 2000 W motor for strong suction power
- New Multi Clean nozzle for thorough cleaning on all floors

Clean air filter system

- EPA10 filter system with AirSeal for healthy air

Effortless cleaning

- ActiveLock couplings to easily adjust to each cleaning task
- Reach all corners thanks to the extra long ergonomic grip
- Soft brush integrated into handle, always ready to use
- Variable power setting

Highlights

EPA10 Clean air system

EPA10 filter and AirSeal capture the finest dust before the air is blown out for a dust-free environment and clean, healthy air.

Power control

The variable power setting allows you to select the optimal level of suction for the different types of surfaces you vacuum.

PowerCyclone 4 Technology

PowerCyclone 4 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber to separate the dust from the air.

Extra long ergonomic grip

This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

2000 Watt motor

2000 W motor generates strong suction power for excellent cleaning results.

ActiveLock couplings

The ActiveLock couplings allow you to easily connect and disconnect the different nozzles and accessories from the telescopic tube while cleaning.

Integrated soft brush

The vacuum cleaner is designed with a soft dusting brush, which is conveniently integrated in the handle of the appliance, always ready to use.

Multi Clean nozzle

The new Multi Clean nozzle delivers a thorough cleaning on all types of floors. The nozzle is designed to seal closely to the floor to ensure a good pick-up of even the fine dust.

Specifications

Performance

Airflow (max): 37 l/s
Input power (IEC): 1800 W
Input power (max): 2000 W
Sound power level: 80 dB
Suction power (max): 370 W
Vacuum (max): 33 kPa

Usability

Action radius: 9 m
Carrying handle: Top and front
Tube type: Metal 2-piece telescopic tube
Wheel type: Rubber
Tube coupling: ActiveLock
Power control: Electronic on appliance

Design

Color: Ink Black

Filtration

Dust capacity: 1.7 L
Exhaust filter: Microfilter
Motor filter: EPA 10 washable filter

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush
Accessory storage: On tubeclip
Standard nozzle: Multi Clean nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 473 x 304 x 301 mm
Weight of product: 6 kg

