

PHILIPS

Bagless vacuum cleaner

EasyClean

1800 W

Parquet

FC8720/01



Take the effort out of cleaning

No bag required

The Philips bagless EasyClean range is designed for those people who want a thorough cleaning result with minimal effort.

Easily removes dirt and dust

- 1800 Watt motor generating max. 300 Watt suction power

Clean air in your home

- Super Clean Air HEPA 12 filter, 99.5% filtration

Easy dust disposal

- Dust bucket can easily be removed and emptied

Easy cleaning, even around furniture

- TriActive nozzle with unique 3-in-1 action

Superior hard-floor cleaning

- Super Parquet nozzle removes 3 x more sticky dirt


Highlights

1800 Watt motor



Philips vacuum cleaner with 1800 Watt motor generating max. 300 Watt suction power to ensure perfect cleaning results.

Super Clean Air HEPA 12 filter



This Super Clean Air HEPA 12 filter catches at least 99.5% of all harmful microscopic vermin that cause respiratory allergies.

Easy-to-empty dust bucket



The bagless vacuum cleaner has a transparent dust bucket that shows the dust removed from your floor and makes it easy to find valuables that are sucked up accidentally.

Super Parquet nozzle



The Super Parquet nozzle allows you to clean hard floors of all kinds thoroughly in one go, without the risk of harming them. Using the absorption capacity of the micro-fibre pads, together with the suction power of the vacuum cleaner, you achieve the best results without requiring any detergents or brushes.

TriActive nozzle



The TriActive nozzle cleans your floor in 3 ways in one go: 1) A larger opening at the tip of the nozzle easily sucks up big bits. 2) It has maximum cleaning efficiency due to optimised airflow through the nozzle. 3) The two side brushes sweep up the dust and dirt closely alongside furniture and walls.

Specifications

Performance

Airflow (max): 34 l/s
 Input power (IEC): 1600 W
 Input power (max): 1800 W
 Noise level (Lc IEC): 79 dB
 Suction power (max): 300 W
 Vacuum (max): 26.5 kPa

Design

Colour: Raven black

Filtration

Exhaust filter: Super Clean Air HEPA 12 filter
 Filter type: Gore-Tex HEPA 10
 Dust capacity: 2 l

Usability

Carrying handle: Top and front
 Tube coupling: Button
 Power control: Electronic on appliance
 Tube type: Metal lacquered 2-piece telescopic tube
 Wheel type: Rubber
 Action radius: 10 m
 Cord length: 7 m

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle
 Accessory storage: On handgrip
 Additional nozzle: Super Parquet nozzle
 Standard nozzle: TriActive nozzle

Weight and dimensions

Weight of product: 6 kg

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

