

# PHILIPS

Vacuum cleaner  
with bag

Performer Expert

AirflowMax technology

Hard floors nozzle

Allergy+

FC8720/09



## Full performance

### Less energy consumption

The new Philips Performer Expert delivers full cleaning performance on all hard floors thanks to the AirflowMax technology and the dedicated hard floors nozzle. Great cleaning results, even as the bag fills up!

#### Outstanding cleaning results

- Revolutionary AirflowMax technology for extreme performance
- Energy efficient motor for high-power results
- A-class performance on hard floors

#### Ultimate convenience

- 5L dust capacity for longer cleaning
- Variable power setting
- SmartLock coupling to easily adjust to each cleaning task

#### Integrated Anti-Allergy system

- HEPA13 with HEPA AirSeal retains more than 99% of dust
- Allergy friendly quality tested by ECARF
- s-bag Ultra Long Performance captures even more fine dust



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## AirflowMax technology



AirflowMax technology maximizes the airflow, allowing the dustbag to unfold uniformly, so you get high performance, even as the bag fills-up!

## High efficiency motor




The high efficiency motor has been optimized to use less energy in order to generate more airflow.

## 5L dust capacity



The specially designed 5L dust chamber allows you to make optimal use of your dust bag, so you can clean for longer.

## Power control



The variable power setting allows you to select the optimal level of suction for the different types of surfaces you vacuum.

## ECARF certified



This vacuum cleaner with HEPA 13 filtration is certified as Allergy friendly by the European Centre for Allergy Research Foundation. The HEPA 13 filter purifies the exhaust air up to 99,95% of allergens from; cat & dog hairs, dust mites or pollen to support an allergy friendly home environment.

## HEPA13 Anti-allergy filtration



HEPA13 filter and AirSeal capture even the finest dust before the air is blown out for a dust-free environment and clean, allergen free air. The exhaust air is even cleaner than the air in the room.

## s-bag Ultra Long Performance



Maintain high cleaning performance for longer, thanks to the XXL 5 liter s-bag Ultra Long Performance. Made of premium, multilayer, non-clogging material, the s-bag Ultra Long Performance guarantees excellent suction power and filtration, lasting up to 80% longer than the standard bag.

## A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Performance

Annual energy consumption: 25 kW-h  
Sound power level: 79 dB  
Input power (IEC): 650 W  
Airflow (max): 30,2 l/s  
Vacuum (max): 16,3 kPa

## Design

Color: Magic purple

## Filtration

Dust capacity: 5 L  
Dust bag type: s-bag Ultra Long Performance  
Exhaust filter: HEPA 13  
Motor filter: Triple layer microfilter  
HEPA Air Seal

## Usability

Action radius: 11 m  
Cord length: 8 m  
Power control: Electronic on appliance  
Tube type: Metal 2-piece telescopic tube  
Tube coupling: SmartLock  
Carrying handle: Top and front  
Dust full indicator

## Nozzles and accessories

Standard nozzle: Hard floors nozzle  
Accessories included: Crevice tool, 2-in-1 brush/small nozzle  
Additional nozzle: Hard floor nozzle

## Sustainability

Packaging: > 90% recycled materials  
User manual: 100% recycled paper

## Weight and dimensions

Weight of product: 5 kg  
Dimensions of product (LxWxH): 500 x 310 x 300 mm

