

# PHILIPS

Vacuum cleaner  
with bag

Performer Expert

AirflowMax technology

TriActiveMax nozzle

Animal+, Allergy+

FC8726/08



## Full performance

### Less energy consumption

The new Philips Performer Expert delivers highest dust pick-up ratings\* on all floors thanks to the AirflowMax technology and unique TriActiveMax nozzle, engineered for highest dust pick-up. Great cleaning results, even as the bag fills up!

#### Perfect for homes with pet hair

- Super Turbo brush, perfect for homes with pet hair

#### Integrated Anti-Allergy system

- Allergy friendly quality tested by ECARF
- HEPA13 with HEPA AirSeal retains more than 99% of dust
- s-bag Ultra Long Performance captures even more fine dust

#### Outstanding cleaning results

- Revolutionary AirflowMax technology for extreme performance
- New 3-in-1 TriActiveMax nozzle maximizes dust pick-up
- Energy efficient motor for high-power results
- A-class performance on hard floors

#### Ultimate convenience

- 5L dust capacity for longer cleaning
- 11m long reach for convenient cleaning



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## AirflowMax technology

AirflowMax technology maximizes the airflow, allowing the dustbag to unfold uniformly, so you get high performance, even as the bag fills-up!

## High efficiency motor

The high efficiency motor has been optimized to use less energy in order to generate more airflow.

## TriActiveMax nozzle

TriActiveMax nozzle with 3-in-1 cleaning actions perfectly seals to the floor to maximize dust pick-up. 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front 3) It sweeps up the dust and dirt closely alongside furniture and walls with its two side brushes.

## Super Turbo brush

The Super Turbo brush allows deep cleaning of carpets, easily removing hair and fluff. The rotating brush inside the nozzle actively removes small dust particles and pet hair, resulting in a better cleaning performance. The wheels of the nozzle prevent damage in case of use on hard floors.

## 5L dust capacity

The specially designed 5L dust chamber allows you to make optimal use of your dust bag, so you can clean for longer.

## Long reach

The 11m reach allows you to clean a larger surface without having to switch the plug.

## HEPA13 Anti-allergy filtration



HEPA13 filter and AirSeal capture even the finest dust before the air is blown out for a dust-free environment and clean, allergen free air. The exhaust air is even cleaner than the air in the room.

## ECARF certified

This vacuum cleaner with HEPA 13 filtration is certified as Allergy friendly by the European Centre for Allergy Research Foundation. The HEPA 13 filter purifies the exhaust air up to 99,95% of allergens from; cat & dog hairs, dust mites or pollen to support an allergy friendly home environment.

## s-bag Ultra Long Performance

Maintain high cleaning performance for longer, thanks to the XXL 5 liter s-bag Ultra Long Performance. Made of premium, multilayer, non-clogging material, the s-bag Ultra Long Performance guarantees excellent suction power and filtration, lasting up to 80% longer than the standard bag.

## A-class on hard floors



This product achieves the highest cleaning performance class on hard floors. 100% of dust is picked up!

# Specifications

## Performance

Annual energy consumption: 27,8 kW·h  
Sound power level: 78 dB  
Input power (IEC): 650 W  
Airflow (max): 30,2 l/s  
Vacuum (max): 16,3 kPa

## Design

Color: Cognac brown

## Filtration

Dust capacity: 5 L  
Dust bag type: s-bag Ultra Long Performance  
Exhaust filter: HEPA 13  
Motor filter: Triple layer microfilter  
HEPA Air Seal

## Usability

Action radius: 11 m  
Cord length: 8 m  
Power control: Electronic on appliance  
Tube type: Metal 2-piece telescopic tube  
Tube coupling: SmartLock  
Wheel type: Rubber  
Carrying handle: Top and front  
Dust full indicator

## Nozzles and accessories

Standard nozzle: TriActiveMax nozzle  
Additional nozzle: Super Turbo brush, Hard floor nozzle  
Accessories included: Crevice tool, 2-in-1 brush/small nozzle

## Weight and dimensions

Weight of product: 5 kg  
Dimensions of product (LxWxH): 500 x 310 x 300 mm

## Sustainability

Packaging: > 90% recycled materials  
User manual: 100% recycled paper



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.