

# PHILIPS

Vacuum cleaner  
with bag

Performer Expert

Energy efficiency class A\*\*

AirflowMax technology

TriActiveMax nozzle

Premium, Allergy+

FC8728/19



## Full performance

### Less energy consumption

The new Philips Performer Expert delivers highest dust pick-up ratings\* on all floors thanks to the AirflowMax technology and unique TriActiveMax nozzle, engineered for highest dust pick-up. Great cleaning results, even as the bag fills up!

#### Outstanding cleaning results

- Energy efficiency class A
- Revolutionary AirflowMax technology for extreme performance
- Energy efficient motor for high-power results
- New 3-in-1 TriActiveMax nozzle maximizes dust pick-up

#### Ultimate convenience

- 5L dust capacity for longer cleaning
- DiamondFlex nozzle rotates 180° for reaching around objects
- Smart cleaning kit with 4 tools, adapted to every need
- SmartLock coupling to easily adjust to each cleaning task
- 11m long reach for convenient cleaning
- Remote control for no bend, with IR wireless technology

#### Integrated Anti-Allergy system


- Allergy friendly quality tested by ECARF
- HEPA13 with HEPA AirSeal retains more than 99% of dust



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## Energy efficiency class A



This vacuum cleaner is engineered to achieve full performance with an energy efficiency class A.

## AirflowMax technology



AirflowMax technology maximizes the airflow, allowing the dustbag to unfold uniformly, so you get high performance, even as the bag fills-up!

## High efficiency motor



The high efficiency motor has been optimized to use less energy in order to generate more airflow.

## TriActiveMax nozzle



TriActiveMax nozzle with 3-in-1 cleaning actions perfectly seals to the floor to maximize dust pick-up. 1) It gently opens the carpet with

its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front 3) It sweeps up the dust and dirt closely alongside furniture and walls with its two side brushes.

## DiamondFlex nozzle



The DiamondFlex nozzle is an ideal tool for reaching around objects and difficult to reach corners. The nozzle has a 180° rotating mechanism and a memory function which ensures it automatically returns to its initial position.

## 5L dust capacity



The specially designed 5L dust chamber allows you to make optimal use of your dust bag, so you can clean for longer.

## Smart cleaning kit



The vacuum cleaner is equipped with a complete set of accessories, tailored to your every need: (1) Long reach tool helps you clean difficult areas like the top of the furniture or high shelves. (2) 3-in-1 tool is perfect for narrow and small spaces. (3) Crevice with small


brush is a tool that easily bends around corners or objects without blocking the airflow. (4) Long brush is ideal for cleaning curtains.

## SmartLock coupling



The unique Philips SmartLock coupling on nozzles and the telescopic tube easily connects, and disconnects, these parts during cleaning. The SmartLock coupling intuitively allows you to adjust the telescopic tube to your preferred height.

## Long reach



The 11m reach allows you to clean a larger surface without having to switch the plug.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Performance

Annual energy consumption: 27.8 kW·h  
Sound power level: 78 dB  
Input power (IEC): 650 W  
Airflow (max): 30,2 l/s l/s  
Vacuum (max): 16,3 kPa

## Design

Color: Chrome red

## Filtration

Dust capacity: 5 L  
Dust bag type: s-bag Ultra Long Performance  
Exhaust filter: HEPA 13  
Motor filter: Triple layer microfilter  
HEPA Air Seal

## Usability

Action radius: 11 m  
Cord length: 8 m  
Power control: Remote control  
Tube type: Metal 2-piece telescopic tube  
Tube coupling: SmartLock  
Wheel type: Rubber  
Carrying handle: Top and front  
Dust full indicator

## Nozzles and accessories

Standard nozzle: TriActiveMax nozzle  
Additional nozzle: DiamondFlex nozzle, Hard floor nozzle

**Accessories included:** Crevice tool, 2-in-1 brush/small nozzle

**Extra accessories:** Smart cleaning kit

## Weight and dimensions

Weight of product: 5 kg  
Dimensions of product (LxWxH): 500 x 310 x 300 mm

## Sustainability

**Packaging:** > 90% recycled materials

**User manual:** 100% recycled paper

