

PHILIPS

Vacuum cleaner
with bag

Performer Silent

Allergy filter

66 dB for quiet vacuuming

12m radius, Cat & Dog mini



FC8743



Maximum performance, minimum sound

Picks-up and locks >99.99%* of dust and allergens

A clean floor makes a healthier home. The new Philips Performer Silent features advanced nozzle technology to capture dirt and fine dust thoroughly, for a healthy environment. At 66 dB, it is also our most silent vacuum cleaner ever.

Superior performance

- High performance with low energy consumption
- Parquet nozzle protects floors from scratching
- Mini Turbo brush for easy (pet) hair and fluff removal

Effortless cleaning

- Vacuum anytime in silence, without disturbing anyone
- Long 12-meter reach goes further without unplugging
- Large 4-liter capacity means fewer bag changes
- Soft brush integrated into handle, always ready to use

Allergy friendly

- Allergy Filter captures 99.9% of all dust - ECARF certified
- Easy s-bags last up to 50% longer

Quality you can trust

- Made in Europe, for quality you can trust

Highlights

A+AAA energy label



This vacuum cleaner is engineered for high performance with low energy consumption. The product is rated A+ on the EU energy label, and achieves class-A on all items in the label: carpet cleaning, hard floor cleaning and dust re-emission.

No-scratch parquet nozzle



Soft brush hairs on our parquet nozzle clean with care and protect your hard floors from scratches.

Mini Turbo brush



The Mini Turbo brush quickly removes (animal) hairs, fluff, and dust from couches, cushions, and other fabrics. This brush is ideal for pet owners.

Silent vacuuming



This vacuum cleaner is engineered for low noise, so you can vacuum anytime without disturbing anyone else in your home. The product features optimized air channels, buffers and a silent motor, so you can enjoy silent vacuuming. Certified by Quiet Mark.

Long 12-meter reach



With a reach of 12 meters from plug to nozzle, it keeps you cleaning longer without unplugging.

Large 4-liter capacity



The large-capacity dust chamber handles a full 4 liters before the bag needs changing.

Integrated brush



A dusting brush attachment is built right into the handle so it's always ready to use for furniture, flat surfaces and upholstery.

Allergy Filter



Our clean-air filter system captures 99.9% of fine dust – including pollen, pet hair and dust mites – for allergy sufferers and anyone demanding a higher level of hygiene. Certified allergy friendly by ECARF.

Easy s-bag



S-bags last up to 50% longer and maintain the full suction power of your vacuum cleaner right up to the moment it's full. One bag fits all models, with a sealing mechanism for tidy disposal.

Specifications

Performance

Input power (IEC): 650 W
Sound power level: 66 dB

Usability

Action radius: 12 m
Carrying handle: Top and front
Cord length: 9 m
Dust full indicator
Tube type: Metal 2-piece telescopic tube
Wheel type: Rubber
Tube coupling: SmartLock
Power control: Electronic on appliance

Design

Color: Pavone Blue

Filtration

Dust bag type: s-bag Ultra Long Performance
Dust capacity: 4 L
Exhaust filter: Allergy filter
Motor filter: Microfilter

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle, Integrated brush
Additional nozzle: Parquet nozzle, Mini turbo brush
Standard nozzle: Multi-purpose nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 470 x 320 x 280 mm
Weight of product: 5.4 kg

