

PHILIPS

Bagless vacuum cleaner

PowerPro

2100W

PowerCyclone 5

HEPA 12 filter

FC8764/11



40% more dust pick-up for a better clean

With PowerCyclone technology and AeroSeal nozzle

The new Philips PowerPro picks up more dust in one go, so your floor gets cleaner with fewer strokes. You can therefore spend more time doing the things you really enjoy.

More dust pick-up for faster cleaning

- PowerCyclone 5 technology separates dust and air in one go
- Powerful 2100 Watt motor for excellent cleaning results
- AeroSeal nozzle captures more dust and fluff per stroke

Extra long reach for convenient cleaning

- More cleaning with less effort

Easy to clean

- Advanced dust container design for hygienic emptying

Highlights

AeroSeal nozzle



The AeroSeal nozzle captures more dust and fluff per stroke thanks to the special designed soleplate. It gently opens up the carpet to remove the dust deep down. Thanks to the optimal sealing the dust is transported into the cyclone with maximum airflow.

2100 Watt motor



This powerful 2100 Watt motor generates max. 370 Watt suction power for excellent cleaning results.


Easy to empty dust container



The dust container is carefully designed to dispose collected dirt without creating a dust cloud. It is one-hand operated and thanks to its

unique shape and smooth surface, you can easily control the emptying of the dust container.

10 m action radius



10 m action radius for cleaning with less effort.

PowerCyclone 5 Technology



PowerCyclone 5 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the air inlet design. 2) The curved airpass quickly accelerates the air in the cyclonic chamber to separate the dust from the air. 3) The optimized exit blades separate dirt from the cyclone and into the dust bucket.

Specifications

Design

Color: Deep black

Filtration

Exhaust filter: Super Clean Air HEPA 12 filter

Motor filter: Double layer

Dust capacity: 2 L

HEPA Air Seal

Nozzles and accessories

Accessories included: Brush, Crevice tool, Small nozzle

Accessory storage: On tubeclip

Standard nozzle: AeroSeal nozzle

Performance

Airflow (max): 38 l/s

Input power (IEC): 1800 W

Input power (max): 2100 W

Noise level (Lc IEC): 80 dB

Suction power (max): 370 W

Vacuum (max): 34 kPa

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Usability

Carrying handle: Top and front

Tube coupling: Easy release

Power control: Electronic on appliance

Tube type: Metal 2-piece telescopic tube

Wheel type: Rubber

Action radius: 10 m

Cord length: 7 m

Weight and dimensions

Weight of product: 5.5 kg

Dimensions of product (LxWxH): 440 x 300 x 290 mm

