

PHILIPS

Bagless vacuum cleaner

PowerPro

2100W

PowerCyclone 5

HEPA 12 filter

Parquet

FC8766/61



40% more dust pick-up for a better clean

With PowerCyclone technology and AeroSeal nozzle

The new Philips PowerPro FC8766 bagless vacuum cleaner picks up more dust in one go, so your floor gets cleaner with fewer strokes. You can therefore spend more time doing the things you really enjoy.

More dust pick-up for faster cleaning

- PowerCyclone technology separates dust and air in one go
- Powerful 2100 Watt motor for excellent cleaning results
- AeroSeal nozzle captures more dust and fluff per stroke

Easy to clean

- Advanced dust container design for easy emptying

Extra long reach for convenient cleaning

- More cleaning with less effort

Highlights

PowerCyclone technology



The PowerCyclone technology delivers best cleaning results in one go through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air.

2100 Watt motor



This powerful 2100 Watt motor generates max. 370 Watt suction power for excellent cleaning results.

AeroSeal nozzle




The AeroSeal nozzle captures more dust and fluff per stroke thanks to the special designed soleplate. It gently opens up the carpet to remove the dust deep down. Thanks to the optimal sealing the dust is transported into the cyclone with maximum airflow.

Easy to empty dust container



The dust container is perfectly designed to dispose dust without creating a dust cloud. Thanks to its unique shape and smooth surface, dust is collected at one side of the container and evenly glides into the dust bin.

10 m action radius



10 m action radius for cleaning with less effort.

Specifications

Design

Color: Metallic titanium

Performance

Input power (max): 2100 W
 Input power (IEC): 1800 W
 Suction power (max): 370 W
 Vacuum (max): 34 kPa
 Airflow (max): 38 l/s
 Noise level (Lc IEC): 80 dB

Filtration

Dust capacity: 2 l
 Exhaust filter: Super Clean Air HEPA 12 filter
 Motor filter: Double layer
 HEPA Air Seal

Usability

Action radius: 10 m
 Cord length: 7 m
 Tube type: Metal 2-piece telescopic tube
 Carrying handle: Top and front
 Tube coupling: Easy release
 Wheel type: Rubber
 Power control: Electronic on appliance

Nozzles and accessories

Standard nozzle: AeroSeal nozzle
 Additional nozzle: Super Parquet nozzle
 Accessories included: Crevice tool, Small nozzle, Brush
 Accessory storage: On tubeclip

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

Weight and dimensions

Weight of product: 5.5 kg
 Dimensions of product (LxWxH): 440 x 300 x 290 mm

