

PHILIPS

Bagless vacuum cleaner

PowerPro

2100W

PowerCyclone 5

Animal

EPA 12 filter



FC8767/61



40% more dust pick-up for a better clean

With PowerCyclone technology and AeroSeal nozzle

The new Philips PowerPro FC8767/01 bagless vacuum cleaner picks up more dust in one go, so your floor gets cleaner with fewer strokes. You can therefore spend more time doing the things you really enjoy.

More dust pick-up for faster cleaning

- AeroSeal nozzle captures more dust and fluff per stroke
- PowerCyclone technology separates dust and air in one go
- Powerful 2100 Watt motor for excellent cleaning results

Easy to clean

- Advanced dust container design for hygienic emptying

Extra long reach for convenient cleaning

- More cleaning with less effort

Highlights

AeroSeal nozzle



The AeroSeal nozzle captures more dust and fluff per stroke thanks to the special designed soleplate. It gently opens up the carpet to remove the dust deep down. Thanks to the optimal sealing the dust is transported into the cyclone with maximum airflow.

PowerCyclone technology



The PowerCyclone technology delivers best cleaning results in one go through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air.

2100 Watt motor




This powerful 2100 Watt motor generates max. 370 Watt suction power for excellent cleaning results.

Easy to empty dust container



The dust container is carefully designed to dispose collected dirt without creating a dust cloud. It is one-hand operated and thanks to its unique shape and smooth surface, you can easily control the emptying of the dust container.

10 m action radius



10 m action radius for cleaning with less effort.

Specifications

Design

Color: Valentin red

Filtration

Exhaust filter: EPA 12 filter
 Motor filter: Foam filter
 Dust capacity: 2 L
 EPA AirSeal

Nozzles and accessories

Accessories included: Brush, Crevice tool, Small nozzle
 Accessory storage: On tubeclip
 Additional nozzle: Turbo brush
 Standard nozzle: AeroSeal nozzle

Performance

Airflow (max): 38 l/s
 Input power (IEC): 1800 W
 Input power (max): 2100 W
 Sound power level: 80 dB
 Suction power (max): 370 W
 Vacuum (max): 34 kPa

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

Usability

Carrying handle: Top and front
 Tube coupling: Universal
 Power control: Electronic on appliance
 Tube type: Metal 2-piece telescopic tube
 Wheel type: Rubber
 Action radius: 10 m
 Cord length: 7 m

Weight and dimensions

Weight of product: 5.5 kg
 Dimensions of product (LxWxH): 440 x 300 x 290 mm

