

PHILIPS

Bagless vacuum cleaner

PowerPro

PowerCyclone 5

TriActiveMax nozzle

EPA 12 filter

FC8769/91



Full performance

Less energy consumption

The new Philips PowerPro vacuum cleaner picks up more dust in one go, so your floor gets cleaner with fewer strokes.

Excellent cleaning results

- PowerCyclone 5 technology separates dust and air in one go
- New 3-in-1 TriActiveMax nozzle maximizes dust pick-up
- Energy efficient motor for high-power results

Extra long reach for convenient cleaning

- More cleaning with less effort

Integrated Anti-Allergy system

- EPA 12 filter with 99.5% filtration of dust

Easy to clean

- Advanced dust container design for easy to emptying



asimpleswitch.com

Highlights

PowerCyclone 5 Technology




PowerCyclone 5 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the air inlet design. 2) The curved airpass quickly accelerates the air in the cyclonic chamber to separate the dust from the air. 3) The optimized exit blades separate dirt from the cyclone and into the dust bucket.

TriActiveMax nozzle




TriActiveMax nozzle with 3-in-1 cleaning actions perfectly seals to the floor to maximize dust pick-up. 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front 3) It sweeps up the dust and dirt closely alongside furniture and walls with its two side brushes.

Energy efficient motor



Highly efficient motor uses less energy to generate airflow. In combination with the nozzle, it delivers top dust pick-up results.

10 m action radius



10 m action radius for cleaning with less effort.

EPA 12 filter



This special outlet filter captures 99.5% of the dust before the air is blown back into your room, ensuring a clean, dust-free, environment.

Easy to empty dust container



The dust container is perfectly designed to dispose dust without creating a dust cloud. Thanks to its unique shape and smooth surface, dust is collected at one side of the container and evenly glides into the dust bin.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Performance

Sound power level: 76 dB
Airflow (max): 22,9 l/s
Vacuum (max): 16,8 kPa
Input power (IEC): 650 W

Design

Color: Deep black and green

Filtration

Exhaust filter: EPA 12 filter
Motor filter: Lifetime washable filter
Dust capacity: 2 L

Usability

Power control: Electronic on appliance
Tube type: Metal 2-piece telescopic tube
Carrying handle: Top and front
Tube coupling: Universal
Wheel type: Rubber
Action radius: 10 m
Cord length: 7 m

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle
Standard nozzle: TriActiveMax nozzle
Accessory storage: On tubeclip
Additional nozzle: Hard floor nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Weight of product: 5.5 kg
Dimensions of product (LxWxH): 550 x 292 x 292 mm

