

PHILIPS

Vacuum cleaner
with bag

HomeHero

1800W

AirflowMax technology

Parquet



FC8912



Live life!

Vacuum cleaner for easy cleaning

Get the job done quickly and easily with Philips HomeHero vacuum cleaner. This cleaner delivers great suction power, dust filtration, and flexible nozzles for thorough cleaning without the hassle.

High cleaning power

- 1800 Watt motor generating max. 325 Watt suction power

Highly efficient anti-allergy system

- EPA AirSeal plus EPA 12 filter

Scratch-protection for parquet floors

- Parquet nozzle with soft brush hairs for scratch-protection

Easy to use all over the house


- Two comfortable carrying handles for extra convenience

Hygienic disposal of dust bag

- Unique Clean Comfort Cassette to avoid contact with dust

Highlights

1800 Watt motor




1800 Watt motor generating max. 325 Watt suction power for perfect cleaning results.

EPA AirSeal, EPA 12 filter




This vacuum cleaner has been designed in such a way that all the air taken in is passed through the EPA 12 filter (99.5% filtration) before it is exhausted. No escape is possible.

Parquet nozzle




No more risk of scratches thanks to this nozzle with soft brush hairs, especially designed to carefully clean your hard floors.

Clean Comfort Cassette



When disposing the dust bag of your Philips vacuum cleaner, there will be no contact with the dust thanks to this patented dust bag holder.

Comfortable carrying handles



This vacuum cleaner has not one, but two carrying handles. When it is on its wheels, there is a handle on top which enables you to easily move the cleaner around with very little bending. The second handle on the front side of the appliance enables you to comfortably carry it around in an upright position.

Specifications

Design

Color: Pistil Red

Filtration

Dust bag type: s-bag
 Exhaust filter: Super Clean Air HEPA 12 washable filter
 Dust capacity: 3 L
 HEPA Air Seal

Nozzles and accessories

Accessories included: Crevice tool
 Accessory storage: On tubeclip
 Additional nozzle: Parquet nozzle
 Standard nozzle: Wheeled all-purpose nozzle

Performance

Airflow (max): 42 l/s
 Input power (IEC): 1600 W
 Input power (max): 1800 W
 Noise level (Lc IEC): 79 dB
 Suction power (max): 325 W
 Vacuum (max): 30 kPa

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

Usability

Carrying handle: Top and front
 Clean Comfort cassette
 Tube coupling: Conical
 Dust full indicator
 Power control: Electronic on appliance
 Tube type: Metal 2-piece telescopic tube
 Wheel type: Rubber
 Action radius: 10 m
 Cord length: 7 m

Weight and dimensions

Weight of product: 5.5 kg

