

Vacuum cleaner
with bag

Performer Ultimate

2200 W

HEPA 13 filter

4L

Smart



FC8924/01



High suction power. For a deep clean.

TriActive LED technology reveals hidden dust

The innovative Philips Performer Ultimate is our most advanced bag vacuum cleaner.

Optimum performance

- AirflowMax technology for continuous strong suction power
- Auto on-off to deliver suction power only when you need it
- Made in Europe
- TriActive LED for deep cleaning results
- 2200 W input power

Advanced deep cleaning

- ErgoGrip remote control handle with built-in control buttons
- On board accessories for quick and thorough cleaning
- Intuitive digital display to get the best performance
- Soft brush integrated into handle, always ready to use
- 30% recycled plastics

Allergy friendly

- HEPA 13 filter
- s-bag Ultra Long Performance captures even more fine dust



Highlights

Auto on-off



The intelligent auto on-off feature will automatically turn your vacuum cleaner on when in use and off when it is not.

On board accessories



The On board accessories includes : - A crevice tool that fits in tighter spots and works well along the edge of baseboards and in hard-to-reach spots, such as vents. - An upholstery tool that has a small, flat head and powerful suction, this attachment works well on fabric surfaces.

Intuitive digital display



The intuitive digital display shows relevant information, enabling you to get the best performance out of your vacuum cleaner: - 4 cleaning settings - Dust Bag Full Indicator - Auto on-off Indicator

Soft brush at your fingertips



A dusting brush attachment is built right into the handle so it's always ready to use for furniture, flat surfaces and upholstery.

Remote control handle



Thanks to the ergonomic remote control, power settings are right by your hand so you can easily switch between power settings to match the place and type of floor surface your vacuuming for more efficient cleaning. Another advantage of the remote control is that you don't have to keep reaching for the main unit so cleaning is easier than ever without compromise on maneuverability.

HEPA 13



Captures more than 99,95% of fine dust, including allergens and irritants such as pollen and dust mites. Developed to meet the specific needs of allergy sufferers, and more generally of people demanding a higher level of filtration

TriActive LED



The new TriActive LED nozzle reveals hidden dust thanks to its exclusive floorlight technology. Thanks to its unique rubber flap structure the brushless nozzle delivers a tangle-free experience for no hair winding. Thanks to its plane shape it offers a lay flat functionality that helps you reach even more areas.



ECARF

Certified as Allergy friendly by the European Centre for Allergy Research Foundation. The exhaust air is purified up to 99,95% of allergens from cat & dog hairs, dust mites or pollen to support an allergy friendly home environment.



5 years warranty

Five years motor warranty When you register your purchase within three months on the Philips website

Specifications

Performance

Input power (IEC): 1800 W
Input power (max): 2200 W
Sound power level: 80 dB
Suction power (max): 550 W

Usability

Action radius: 11 m
Carrying handle: Front
Tube type: Aluminium 2-P telescopic tube
Wheel type: Rubber
Tube coupling: SmartLock
Power control: ErgoGrip remote control
Digital Dustbag full indicator

Design

Color: Silver titanium

Filtration

Dust bag type: s-bag Ultra Long Performance
Dust capacity: 4 L
Exhaust filter: HEPA13 filter

Sustainability

Packaging: > 75% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 475 x 300 x 280 mm
Weight of product: 6.2 kg

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush, Small brush
Standard nozzle: TriActive LED nozzle
Extra accessories: ErgoGrip remote control

