

# PHILIPS

Vacuum cleaner  
with bag

Performer Ultimate

99.9% dust pick-up

900W

4L



FC8955/09



## Full performance. For a deep clean. TriActive LED technology reveals hidden dust.

The innovative Philips Performer Ultimate is our most advanced bag vacuum cleaner.

### Optimum performance

- AirflowMax technology for continuous strong suction power
- TriActive LED for deep cleaning results
- CarpetClean for efficient cleaning on soft floors
- Auto on-off to deliver suction power only when you need it
- Made in Europe

### Advanced deep cleaning

- ErgoGrip remote control handle with built-in control buttons
- On board accessories for quick and thorough cleaning
- Intuitive digital display to get the best performance
- Soft brush integrated into handle, always ready to use
- 30% recycled plastics

### Allergy friendly

- Allergy filter retains >99.9% of particles, ECARF certified

### Remarkable results



# Highlights

## AirflowMax technology



The unique AirflowMax technology keeps the suction power strong for long to use the bag to the very end. The technology is build around the optimization of three key elements: 1) Unique ribs profile inside the dust chamber to maximize airflow around the dustbag and enable the use of the entire bag surface. 2) Specially designed dust chamber capacity that allows the dustbag to fully unfold uniformly. 3) High quality, non-clogging fiber dustbag that absorbs dust without blocking the pores, thus avoiding reduction in suction power.

## TriActive LED



The new TriActive LED nozzle reveals hidden dust thanks to its exclusive floorlight technology. Thanks to its unique rubber flap structure the brushless nozzle delivers a tangle-free experience for no hair winding. Thanks to its plane shape it offers a lay flat functionality that helps you reach even more areas.

## CarpetClean



The CarpetClean is ideal for deep clean, this nozzle is suitable for the toughest carpet clean and delivers high dust pick up on soft floors.

## Auto on-off



The intelligent auto on-off feature will automatically turn your vacuum cleaner on when in use and off when it is not

## Made in Europe



The innovative Performer Ultimate is made in Europe according to Philips' high quality standards

## Remote control handle



Thanks to the ergonomic remote control, power settings are right by your hand so you can easily switch between power settings to match

the place and type of floor surface your vacuuming for more efficient cleaning. Another advantage of the remote control is that you don't have to keep reaching for the main unit so cleaning is easier than ever without compromise on maneuverability.



## ECARF

Certified as Allergy friendly by the European Centre for Allergy Research Foundation. The exhaust air is purified up to 99,95% of allergens from cat & dog hairs, dust mites or pollen to support an allergy friendly home environment.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



## 5 years warranty

Five years motor warranty Register at [philips.com/welcome](http://philips.com/welcome) within 3 months of purchase to enjoy 5-year warranty on the motor for free!

# Specifications

## Performance

Input power (max): 900 W  
Airflow (max): 35 l/s  
Input power (IEC): 750 W  
Sound power level: 75 dB  
Suction power (max): 220 W  
Vacuum (max): 15 kPa

## Usability

Action radius: 11 m  
Carrying handle: Front  
Tube type: Aluminium 2-P telescopic tube  
Wheel type: Rubber

Tube coupling: SmartLock  
Power control: Remote control  
Digital Dustbag full indicator

## Design

Color: Silver titanium

## Filtration

Dust bag type: s-bag Ultra Long Performance  
Dust capacity: 4 L  
Exhaust filter: Allergy filter

## Nozzles and accessories

Accessories included: Crevice tool, Integrated brush, Small brush  
Additional nozzle: Carpet Clean nozzle  
Extra accessories: ErgoGrip remote control  
Standard nozzle: TriActive LED nozzle

## Sustainability

Packaging: > 75% recycled materials  
User manual: 100% recycled paper

## Weight and dimensions

Dimensions of product (LxWxH): 475 x 300 x 280 mm  
Weight of product: 6.2 kg

