

PHILIPS

Vacuum cleaner
with bag

Studio

Animal



FC9086/01



Small in size, big in power

Studio is for people who would like the performance of a big vacuum cleaner combined with the compactness of a small one. Its size, carrying handles and 8 m cord offer great flexibility, so you can quickly move through your home.

Excellent cleaning results

- 2000 Watt motor generating max. 400 Watt suction power

Carefree cleaning

- Ergonomically designed ComfortControl handle

Easy to use all over the house

- Two comfortable carrying handles for extra convenience

Outstanding results on carpets and furniture


- Turbo Brush nozzle removes 25% more hairs and dust

Easy cleaning, even around furniture

- Tri-active nozzle with unique 3-in-1 action

Highlights

2000 Watt motor



This powerful 2000 Watt motor generates max. 400 Watt suction power for excellent cleaning results.

ComfortControl handle



This ergonomically designed handle helps to prevent strain on wrists. It offers effortless single handed manoeuvring. Enjoy easier cleaning.

Comfortable carrying handles



This vacuum cleaner has not one, but two carrying handles. When it is on its wheels, there is a handle on top which enables you to easily move the cleaner around with very little

bending. The second handle on the front side of the appliance enables you to comfortably carry it around in an upright position.

Turbo Brush nozzle



The Turbo Brush nozzle allows deep cleaning of carpets and quick hair and fluff removal from carpets. The rotating brush actively removes small dust particles and hairs, resulting in a 25% better cleaning performance on carpets. The wheels of the nozzle prevent damage during use on hard floors.

Tri-active nozzle

This unique nozzle is aerodynamically designed for maximum cleaning efficiency, has side brushes to remove dust from corners and curves, and has a front opening to pick up the big bits. Each stroke will deliver an immediate clean result.

HEPA AirSeal, HEPA 13 filter



This Philips vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

Specifications

Design

Colour: Vermilion and raven black

Filtration

Dust bag type: s-bag Anti-odour

Dust capacity: 3 l

Exhaust filter: Ultra Clean Air HEPA 13 washable filter

HEPA AirSeal

Nozzles and accessories

Accessories: Crevice tool, Small nozzle

Accessory storage: On handgrip

Additional nozzle: Turbo brush

Standard nozzle: TriActive nozzle

Performance

Airflow (max): 40 l/s

Input power (IEC): 1800 W

Input power (max): 2000 W

Noise level (Lc IEC): 78 dB

Suction power (max): 400 W

Vacuum (max): 30 kPa

Usability

Action radius: 11 m

Carrying handle: Top and front

Clean Comfort cassette

Cord length: 8 m

Tube coupling: Button

Dust bag full indicator

Power control: Electronic on appliance

Tube type: Metal lacquered 2-piece telescopic tube

Wheel type: Rubber

