

PHILIPS

Vacuum cleaner
with bag

Studio

EnergyCare

RemoteControl

FC9089/01



Greener every day

Save 30% energy with highly efficient HD motor*

Studio is for people who would like the performance of a big vacuum cleaner combined with the compactness of a small one. The new highly efficient HD motor uses up to 30% less energy, while keeping the excellent suction power.

Low power consumption, high-power results

- New 1250 Watt HD motor generates up to 350 Watt suction power

Carefree cleaning

- Ergonomically designed ComfortControl handle

Change controls without bending down

- Fingertip controls in the handle

Easy to use all over the house

- Two comfortable carrying handles for extra convenience

Easy cleaning, even around furniture

- Tri-active nozzle with unique 3-in-1 action

Highlights

New 1250 Watt HD motor



The highly efficient 1250 Watt HD (High Density) motor generates up to 350 Watts of suction power, which means that you use 30% less energy without compromising on the cleaning result.

ComfortControl handle



This ergonomically designed handle helps to prevent strain on wrists. It offers effortless single handed manoeuvring. Enjoy easier cleaning.

Fingertip controls



Via the buttons in the handle you can easily operate your vacuum cleaner — without bending!

Comfortable carrying handles



This vacuum cleaner has not one, but two carrying handles. When it is on its wheels, there is a handle on top which enables you to easily move the cleaner around with very little bending. The second handle on the front side of the appliance enables you to comfortably carry it around in an upright position.

Tri-active nozzle

This unique nozzle is aerodynamically designed for maximum cleaning efficiency, has side brushes to remove dust from corners and curves, and has a front opening to pick up the big bits. Each stroke will deliver an immediate clean result.

HEPA AirSeal, HEPA 13 filter



This vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

Specifications

Design

Colour: Copper and dark raven

Filtration

Dust bag type: s-bag

Dust capacity: 3 l

Exhaust filter: Ultra Clean Air HEPA 13 washable filter

HEPA AirSeal

Nozzles and accessories

Accessories: Crevice tool, Small nozzle

Accessory storage: On handgrip

Standard nozzle: TriActive nozzle

Performance

Airflow (max): 39 l/s

Input power (IEC): 1250 W

Noise level (Lc IEC): 78 dB

Suction power (max): 350 W

Vacuum (max): 28 kPa

Usability

Action radius: 11 m

Carrying handle: Top and front

Clean Comfort cassette

Cord length: 8 m

Tube coupling: Button

Dust bag full indicator

Power control: Electronic on handgrip

Tube type: Metal lacquered 2-piece telescopic tube

Wheel type: Rubber

