

# Floor Care range 2002



FC 9102 FC 9104 FC 9106 FC 9108 FC 9110 FC 9112 FC 9114

## SPECIALIST

	Reach & Clean FC 9102	Hygiene FC 9104	Hard Floor FC 9106	Carpet FC 9108	Animal Care FC 9110	Control FC 9112	Multi FC 9114
<b>Technical data</b>							
Max input power (W)	1800	1800	1800	1800	1800	1800	1800
IEC input power (W)	1600	1600	1600	1600	1600	1600	1600
Electronics	Slide	Slide	Slide	Slide	Slide	IR RMC	Slide
Tubes	Telescopic	Telescopic	Telescopic	Telescopic	Telescopic	Telescopic	Telescopic
Filters	7	7 (Hepa)	7	7	7 (Acti.Carb.)	7	7
Dust bag capacity (L)	3	3	3	3	3	3	3
Acc. Bridge storage	●	●	●	●	●	●	●
Cord length (M)	7	7	7	7	7	9	9
Dust bag full indicator	●	●	●	●	●	●	●
Filter Full indicator	-	●	-	-	-	-	-
Reach & Clean Nozzle	●	●	●	●	●	●	●
Additional nozzle	-	Twist&Clean	Turbo Brush	Turbo Brush	Twist&Clean	Animal Care Br.	Turbo Brush
Small accessories	3	3	3	3	3	3	3
	Small Brush	Small Brush	Small Brush	Small Brush	Small Brush	Small Brush	Small Brush
	Crevice nozzle	Crevice nozzle	Crevice nozzle	Crevice nozzle	Crevice nozzle	Crevice nozzle	Crevice nozzle
	Small nozzle	Small nozzle	Small nozzle	Small nozzle	Small nozzle	Small nozzle	Small nozzle
Act. coupling basic	●	●	-	-	-	-	-
Act. coupling luxury	-	-	●	●	●	●	●
Wheels	Plastic	Plastic	Rubber	Plastic	Plastic	Rubber	Rubber
Colour upper parts (ABS)	Ice Blue	Mint Green	Cherry Wood	Daybreak	Crushed	Ice Blue metallic	Metallic
				Purple	Berry	(partly)	Mauve (full)
Colour lower parts	Light Grey	Light Grey	Light Grey	Light Grey	Light Grey	Light Grey	Light Grey
Wheel colour	Light Grey	Light Grey	Cherry Wood	Light Grey	Light Grey	Ice Blue	Mauve



FC 9002 FC 9003 FC 9006 FC 9007 FC 9008 FC 9010 FC 9012

## UNIVERSE

	FC 9002	FC 9003	FC 9006	FC 9007	FC 9008	FC 9010	FC 9012
<b>Technical data</b>							
Max input power (W)	1700	1700	1700	1700	1700	1700	1700
IEC input power (W)	1500	1500	1500	1500	1500	1500	1500
Electronics	Turn	Turn	Turn	Turn	Turn	Turn	Turn
Tubes	Conical	Conical	Telescopic	Telescopic	Telescopic	Telescopic	Telescopic
Filters	6	6	6	6	6 (HEPA)	6	6
Dust bag cap. (L)	3	3	3	3	3	3	3
Acc. Bridge storage	●	●	●	●	●	●	●
Cord length (M)	7	7	7	7	7	9	9
Dust bag full indicator	●	●	●	●	●	●	●
Nozzle	All purpose wheeled	All purpose wheeled	All purpose wheeled	All purpose wheeled	All purpose wheeled/wheeled	All purpose wheeled	All purpose wheeled
Add. nozzles	-	-	-	-	-	Turbo brush	Twist&Clean
Small accessories	2	2	2	2	2	2	2
	Crevice nozzle	Crevice nozzle	Crevice nozzle	Crevice nozzle	Crevice nozzle	Crevice nozzle	Crevice nozzle
	Small nozzle	Small nozzle	Small nozzle	Small nozzle	Small nozzle	Small nozzle	Small nozzle
Coupling	Conical	Conical	Button	Button	Button	Button	Button
Wheels	Plastic	Plastic	Plastic	Plastic	Plastic	Plastic	Plastic
Colour upper parts (ABS)	Apple Green	Mellow Yellow	Soft Red	Mellow Yellow	Misty Green	Fresh Blue	Fresh Blue
Colour lower parts	Dark Grey	Dark Grey	Dark Grey	Dark Grey	Dark Grey	Dark Grey	Dark Grey
Wheel colour	Dark Grey	Dark Grey	Dark Grey	Dark Grey	Dark Grey	Dark Grey	Dark Grey



FC 6044 FC 6047 FC 6064 FC 6067 FC 6076 FC 6082

## HANDHELDS

	FC 6044 (Dry)	FC 6047 (Dry)	FC 6064 (Dry)	FC 6067(W&D)	FC 6076 (W&D)	FC 6082 (W&D)
<b>Technical data</b>						
Voltage	2.4V	3.6V	3.6V	3.6V	4.8V	4.8V
No of Batteries	2	3	3	3	4	4
No of speeds	1	1	2	2	2	2
Air flow rate (m³/min.)	0.25	0.25	0.47	0.47	0.50	0.57
Dry volume cap. (ml)	300	300	300	300	300	300
Wet volume cap. (ml)	-	-	-	100	100	100
Run time	9	9.5	9.5	9.5	11	11
Charging indicator	●	●	●	●	●	●
Fluff collector	●	●	●	-	-	-
Small brush	-	-	-	-	-	-
Crevice tool	-	-	●	●	●	●
Squeegee	-	-	-	●	●	●
Extension pole/floor nozzle	-	-	-	-	-	●
Color	Comfort white	Sky Blue	Ivory/Pearl Blue	Ivory/Pearl Blue	Petrol Green	Bordeaux
Position life cycle	Beginning	Beginning	Beginning	Beginning	Beginning	Beginning



**PHILIPS**

*Let's make things better.*

Product specification is subject to change without prior notice.  
For concern use only.  
D.A.P. Division, Amersfoort, Holland.



FC 8400 FC 8402 FC 8404 FC 8406 FC 8408 FC 8410 FC 8412

**CITY LINE**

	Miami FC 8400	Barcelona FC 8402	Roma FC 8404	Monte Carlo FC 8406	Helsinki FC 8408	Tokyo FC 8410	Chicago FC 8412
<b>Technical data</b>							
Max input power (W)	1700	1700	1700	1700	1700	1700	1700
IEC input power (W)	1500	1500	1500	1500	1500	1500	1500
Electronics	–	●	●	●	●	●	IR RMC
Tubes	Chrome	Chrome	Telescopic	Telescopic	Telescopic	Telescopic	Telescopic
Filters	5	5	5	5	5 (Hepa)	5	5
Dust bag capacity (L)	2	2	2	2	2	2	2
Park assist	–	–	–	–	–	–	–
Storage assist	●	●	●	●	●	●	●
Cord length (M)	6	6	6	6	6	6	6
Cord winder	●	●	●	●	●	●	●
Dust bag full indicator	●	●	●	●	●	●	●
Reach & Clean Nozzle	–	–	–	●	●	●	●
Additional nozzle	–	–	–	–	–	Twist&Clean	Twist&Clean
Accessories	Crevice on board Small nozzle Brush	Crevice on board Small nozzle Brush	Crevice on board Small nozzle Brush	Crevice on board Small nozzle Brush	Crevice on board Small nozzle Brush	Crevice on board Small nozzle Brush	Crevice on board Small nozzle Brush
Act. coupling basic	–	–	–	●	●	●	●
Colour upper parts (ABS)	Sunny Lime	Lavender	Apricot Gold	Pearl Rouge	Icicle Gold	Sunny Rose	Violet Shadow
Colour lower parts	Canyon Grey	Canyon Grey	Canyon Grey	Canyon Grey	Canyon Grey	Canyon Grey	Canyon Grey
Colour rear wheels	Canyon Grey	Canyon Grey	Canyon Grey	Canyon Grey	Canyon Grey	Canyon Grey	Canyon Grey



HR 8352 HR 8353 HR 8356 HR 8358 HR 8360 HR 8362 HR 8364

**IMPACT**

	HR 8352	HR 8353	HR 8356	HR 8358	HR 8360	HR 8362	HR 8364
<b>Technical data</b>							
Max input power (W)	1300	1300	1400	1400	1500	1500	1500
IEC input power (W)	1100	1100	1200	1200	1300	1300	1300
Noise (dBA)	80	80	80	80	80	80	80
Electronics	–	●	–	●	●	●	●
Tubes	Metal	Metal	Metal	Metal	Metal	Chrome	Telescopic
Filters	5	5	5	5	5	5	5
Dust bag capacity (L)	2	2	2	2	2	2	2
Cord length (M)	5	5	5	5	6	6	6
Dust bag full indicator	●	●	●	●	●	●	●
Nozzle	Standard	Standard	Standard	Standard	Wheeled	Wheeled	Wheeled
Accessories	2 in 1	2 in 1	2 in 1	2 in 1	2 in 1	2+1	2+1
Type of acc. storage	under carrying handle	under carrying handle	under carrying handle	under carrying handle	under carrying handle	under carrying handle	under carrying handle
Colour upper parts (ABS)	Sky Blue	Summer Red	Summer Red	Lemon Yellow	Apple Green	Blueberry Purple	Blueberry Purple
Colour rear wheels	Dark Purple	Summer Red	Summer Red	Dark Purple	Dark Purple	Dark Purple	Dark Purple
Colour lower parts	Dark Purple	Dark Purple	Dark Purple	Dark Purple	Dark Purple	Dark Purple	Dark Purple



HR 6328 HR 6329

**ECONOMY**

	HR 6328	HR 6329
<b>Technical data</b>		
Max input power (W)	1150	1150
IEC input power (W)	1050	1050
Suction power (W)	190	190
Noise (dBA)	80	80
Electronics	–	●
Tubes	Metal	Metal
Filters	5	5
Dust bag capacity (L)	2.3	2.3
Cord length (M)	5	5
Dust dust full indicator	●	●
Nozzle	Standard	Standard
Accessories	2 in 1	2 in 1
Type of accessory storage	Combi acc. under carr. handle	Combi acc. under carr. handle
Colour upper parts (ABS)	Metallic Blue	Metallic Silver
Colour rear wheels	Dark Grey	Dark Grey
Colour lower parts	Dark Grey	Dark Grey