

# PHILIPS

Vacuum cleaner  
with bag

Performer

ParquetCare

RemoteControl

FC9166/01



## The highest suction power ever

500 Watt suction power for effortless cleaning

The highest suction power ever, resulting in effortless cleaning: this is what the FC916x range is all about. Combined with a hygienic filter and easy dustbag removal system the FC916x range takes care of all your dust and dirt.

### **Superior cleaning**

- 2200 Watt motor generating max. 500 Watt suction power

### **Traps dust and allergens inside**

- Ultra Clean Air HEPA 13 filter, 99.95% filtration

### **Long lasting dust pickup**

- s-bag in XXL 4 liter capacity for long-lasting performance

### **Suction power control at your fingertips**

- Handy remote control to change the suction power

### **Superior hard-floor cleaning**

- Super parquet nozzle removes 3 x more sticky dirt

# Highlights

## Powerful cleaning



Highly efficient 2200 Watt motor generates max. 500 Watt suction power for perfect cleaning results.

## s-bag in XXL 4 liter



This large dust bag capacity allows you to make optimal use of your dust bag, which means you have to change your dust bag less frequently.

## Handy remote control



Handy remote control to change the suction power with your fingertips and without bending.

## Super parquet nozzle removes 3 x more sticky dirt



Super parquet nozzle removes 3 x more sticky dirt

## TriActive nozzle



The TriActive nozzle cleans your floor in 3 ways in one go: 1) A larger opening at the tip of the nozzle easily sucks up big bits. 2) It has maximum cleaning efficiency due to optimized airflow through the nozzle. 3) The two side brushes sweep up the dust and dirt closely alongside furniture and walls.

# Specifications

## Design

Color: Translucent smoked black

## Filtration

Dust bag type: s-bag  
Exhaust filter: Ultra Clean Air HEPA 13 washable filter  
Dust capacity: 4 L

## Nozzles and accessories

Accessories included: Crevice tool, Small nozzle

Accessory storage: On handgrip

Additional nozzle: Super Parquet nozzle

Standard nozzle: TriActive nozzle

## Performance

Airflow (max): 47 l/s  
Input power (IEC): 2000 W  
Input power (max): 2200 W  
Noise level (Lc IEC): 78 dB  
Suction power (max): 500 W  
Vacuum (max): 34 kPa

## Usability

Carrying handle: Top and front

Clean Comfort cassette

Cord length: 9 m

Tube coupling: Button

Dust full indicator

Power control: Electronic on handgrip

Tube type: Metal lacquered 2-piece telescopic tube

Wheel type: Rubber

## Weight and dimensions

Weight of product: 6.3 kg

Dimensions of product (LxWxH): 500 x 320 x 280 mm

