

# PHILIPS

Vacuum cleaner  
with bag

Performer

ParquetCare

RemoteControl

FC9166/01



## The highest suction power ever

500 Watt suction power for effortless cleaning

The highest suction power ever, resulting in effortless cleaning: this is what the FC916x range is all about. Combined with a hygienic filter and easy dustbag removal system the FC916x range takes care of all your dust and dirt.

### **Superior cleaning**

- 2200 Watt motor generating max. 500 Watt suction power

### **Long lasting dust pickup**

- s-bag in XXL 4 liter capacity for long-lasting performance

### **Suction power control at your fingertips**

- Handy remote control to change the suction power

### **Superior hard-floor cleaning**

- Super parquet nozzle removes 3 x more sticky dirt

### **Easy cleaning, even around furniture**

- Tri-active nozzle with unique 3-in-1 action

# Highlights

## Powerful cleaning



Highly efficient 2200 Watt motor generates max. 500 Watt suction power for perfect cleaning results.

## s-bag in XXL 4 liter



This large dust bag capacity allows you to make optimal use of your dust bag, which means you have to change your dust bag less frequently.

## Handy remote control



Handy remote control to change the suction power with your fingertips and without bending.

## Super parquet nozzle removes 3 x more sticky dirt



Super parquet nozzle removes 3 x more sticky dirt

## Tri-active nozzle



This unique nozzle is aerodynamically designed for maximum cleaning efficiency, has side brushes to remove dust from corners and curves, and has a front opening to pick up the big bits. Each stroke will deliver an immediate clean result.

# Specifications

## Design

**Color:** Translucent smoked black

## Performance

**Input power (max):** 2200 W

**Input power (IEC):** 2000 W

**Suction power (max):** 500 W

**Vacuum (max):** 34 kPa

**Airflow (max):** 47 l/s

**Noise level (Lc IEC):** 78 dB

## Filtration

**Dust capacity:** 4 l

**Dust bag type:** s-bag

**Exhaust filter:** Ultra Clean Air HEPA 13 washable filter

## Usability

**Tube type:** Metal lacquered 2-piece telescopic tube

**Carrying handle:** Top and front

**Dust bag full indicator:**

**Clean Comfort cassette:**

**Coupling:** Button

**Park or storage assist:** Back and bottom

**Wheel type:** Rubber

**Power control:** Electronic on handgrip

**Cord length:** 9 m

## Nozzles and accessories

**Standard nozzle:** TriActive nozzle

**Additional nozzle:** Super Parquet nozzle

**Accessories:** Crevice tool, Small nozzle

**Accessories storage:** On handgrip

## Weight and dimensions

**Weight:** 6.3 kg