

PHILIPS

Vacuum cleaner
with bag

Performer

2200W

500W suction power

HEPA 13 washable filter

FC9172/01



The highest suction power ever

500 Watt suction power for effortless cleaning

The highest suction power ever, resulting in effortless cleaning: this is what the Philips Performer is all about. Combined with a hygienic filter and easy dustbag removal system the Performer takes care of all your dust and dirt.

Superior cleaning

- 2200 Watt motor generating max. 500 Watt suction power

Highly efficient anti-allergy system

- HEPA AirSeal plus HEPA 13 filter
- ECARF Seal of Quality for trusted results

Long lasting dust pickup

- s-bag in XXL 4 liter capacity for long-lasting performance

Superior hard-floor cleaning

- Super Parquet nozzle removes 3 x more sticky dirt

Easy cleaning, even around furniture

- TriActive nozzle with unique 3-in-1 action

Highlights

Powerful cleaning



Highly efficient 2200 Watt motor generates max. 500 Watt suction power for perfect cleaning results.

HEPA AirSeal, HEPA 13 filter



This Philips vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

s-bag in XXL 4 liter



This large dust bag capacity allows you to make optimal use of your dust bag, which means you have to change your dust bag less frequently.

Super Parquet nozzle



The Super Parquet nozzle allows you really clean hard floors of all kinds in one go, without the risk of harming them. Using the absorption capacity of the micro-fibre pads, together with the suction power of the vacuum cleaner, you achieve maximum result without requiring any detergents or brushes.

Specifications

Design

Color: Emperor red

Filtration

Dust bag type: s-bag
Exhaust filter: Ultra Clean Air HEPA 13 filter
Dust capacity: 4 L
HEPA Air Seal

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle

Additional nozzle: Super Parquet nozzle

Standard nozzle: TriActive nozzle

Performance

Airflow (max): 47 l/s
Input power (IEC): 2000 W
Input power (max): 2200 W
Noise level (Lc IEC): 78 dB
Suction power (max): 500 W
Vacuum (max): 34 kPa

Usability

Carrying handle: Top and front

Clean Comfort cassette

Tube coupling: Button

Dust full indicator

Tube type: Metal 2-piece telescopic tube

Wheel type: Rubber

Action radius: 10 m

Cord length: 7 m

Weight and dimensions

Weight of product: 6.3 kg

Dimensions of product (LxWxH): 500 x 320 x 280 mm

