

# PHILIPS

Vacuum cleaner  
with bag

Performer

2200 W

500W suction power

HEPA 13 filter

Turbo brush



FC9174/61



## The highest suction power ever

500 Watt suction power for effortless cleaning

The highest suction power ever, resulting in effortless cleaning: this is what the Philips Performer is all about. Combined with a hygienic filter and easy dustbag removal system the Performer takes care of all your dust and dirt.

### Superior performance

- 2200 Watt motor generating max. 500 Watt suction power
- TriActive nozzle applies 3 cleaning actions in one go
- Turbo Brush nozzle for removing pet hair

### Effortless cleaning

- Long 10-meter reach goes further without unplugging
- Large 4-liter capacity means fewer bag changes

### Allergy friendly

- HEPA13 filter captures 99.9% of all dust - ECARF certified
- Easy s-bags last up to 50% longer

### Quality you can trust

- Made in Europe, for quality you can trust

# Highlights

## Powerful cleaning



Highly efficient 2200 Watt motor generates max. 500 Watt suction power for perfect cleaning results.

## TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It sweeps up the dust and dirt alongside furniture and walls with its two side brushes.

## Turbo Brush



The rotating Turbo Brush is specifically designed for deep cleaning of carpets, easily removing hair and fluff. The rotating brush inside the nozzle actively removes small dust particles and pet hair.

## Long 10-meter reach




With a reach of 10 meters from plug to nozzle, it keeps you cleaning longer without unplugging.

## Large 4-liter capacity



The large-capacity dust chamber handles a full 4 liters before the bag needs changing.

## HEPA13 filter



Our HEPA13 filter system captures 99.9% of fine dust – including pollen, pet hair and dust mites – for allergy sufferers and anyone demanding a higher level of hygiene. Certified allergy friendly by ECARF.

## Easy s-bag



S-bags last up to 50% longer and maintain the full suction power of your vacuum cleaner right up to the moment it's full. One bag fits all models, with a sealing mechanism for tidy disposal.

## Made in Europe



This product is designed, tested and manufactured in Europe, so you can enjoy the highest level of quality.

# Specifications

## Design

Color: Emperor red

## Filtration

Dust bag type: s-bag

Exhaust filter: Ultra Clean Air HEPA 13 filter

Dust capacity: 4 L

HEPA Air Seal

## Nozzles and accessories

Accessories included: Crevice tool, Small nozzle

Standard nozzle: TriActive nozzle

## Performance

Airflow (max): 47 l/s

Input power (IEC): 2000 W

Input power (max): 2200 W

Noise level (Lc IEC): 78 dB

Suction power (max): 500 W

Vacuum (max): 34 kPa

## Usability

Carrying handle: Top and front

Clean Comfort cassette

Tube coupling: Button

Dust full indicator

Tube type: Metal lacquered 2-piece telescopic

tube

Wheel type: Rubber

Action radius: 10 m

Cord length: 7 m

## Weight and dimensions

Weight of product: 6.3 kg

Dimensions of product (LxWxH): 500 x 320 x 280 mm

