

PHILIPS

Vacuum cleaner
with bag

Performer

1250W

375W suction power

HEPA 13 washable filter

Parquet

FC9178/01



Greener every day

Save 35% energy with highly efficient HD motor*

The highest suction power ever, resulting in effortless cleaning: this is what the Philips Performer is all about. The new highly efficient HD motor uses up to 35% less energy, while keeping the excellent suction power.

Low power consumption, high-power results

- New 1250 Watt HD motor generates max. 375 Watt suction power

Less waste in the environment

- At least 60% of plastics is sustainable

Carefree cleaning

- Ergonomically designed ComfortControl handle

Superior hard-floor cleaning

- Super Parquet nozzle removes 3 x more sticky dirt


Highly efficient anti-allergy system

- HEPA AirSeal plus HEPA 13 filter
- ECARF Seal of Quality for trusted results



Highlights

New 1250 Watt HD motor



Highly efficient 1250 Watt HD (High Density) motor generates 375 Watt max. suction power, which means that you use 35% less energy without giving in on the cleaning result.

ComfortControl handle



This ergonomically designed handle helps to prevent strain on wrists. It offers effortless single handed manoeuvring. Enjoy easier cleaning.

Super Parquet nozzle



The Super Parquet nozzle allows you really clean hard floors of all kinds in one go, without the risk of harming them. Using the absorption capacity of the micro-fibre pads, together with the suction power of the vacuum cleaner, you achieve maximum result without requiring any detergents or brushes.

HEPA AirSeal, HEPA 13 filter



This Philips vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

Specifications

Design

Color: Greige

Filtration

Dust bag type: s-bag
 Exhaust filter: Ultra Clean Air HEPA 13 washable filter
 Dust capacity: 4 L
 HEPA Air Seal

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle
 Accessory storage: On handgrip
 Additional nozzle: Super Parquet nozzle
 Standard nozzle: TriActive nozzle

Performance

Airflow (max): 39 l/s
 Input power (IEC): 1250 W
 Input power (max): 1250 W
 Noise level (Lc IEC): 78 dB
 Suction power (max): 375 W
 Vacuum (max): 28 kPa

Usability

Carrying handle: Top and front
 Clean Comfort cassette
 Tube coupling: Button
 Dust full indicator
 Tube type: Metal lacquered 2-piece telescopic tube
 Wheel type: Rubber
 Action radius: 12 m
 Cord length: 7 m

Weight and dimensions

Weight of product: 6.5 kg
 Dimensions of product (LxWxH): 500 x 320 x 280 mm

