

PHILIPS

Vacuum cleaner
with bag

Performer

EnergyCare

ParquetCare

FC9178/01



Greener every day

Save 35% energy with highly efficient HD motor*

The highest suction power ever, resulting in effortless cleaning: this is what the Philips Performer is all about. The new highly efficient HD motor uses up to 35% less energy, while keeping the excellent suction power.

Low power consumption, high-power results

- New 1250 Watt HD motor generates max. 375 Watt suction power

Less waste in the environment

- At least 60% of plastics are sustainable

Carefree cleaning

- Ergonomically designed ComfortControl handle

Superior hard-floor cleaning

- Super Parquet nozzle removes 3 x more sticky dirt


Highly efficient anti-allergy system

- HEPA AirSeal plus HEPA 13 washable filter



Highlights

New 1250 Watt HD motor



Highly efficient 1250 Watt HD (High Density) motor generates 375 Watt max. suction power, which means that you use 35% less energy without giving in on the cleaning result.

ComfortControl handle



This ergonomically designed handle helps to prevent strain on wrists. It offers effortless single handed manoeuvring. Enjoy easier cleaning.

Super Parquet nozzle



The Super Parquet nozzle allows you to clean hard floors of all kinds thoroughly in one go, without the risk of harming them. Using the

absorption capacity of the micro-fibre pads, together with the suction power of the vacuum cleaner, you achieve the best results without requiring any detergents or brushes.

HEPA AirSeal, HEPA 13 filter



This vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

Tri-active nozzle



This unique nozzle is aerodynamically designed for maximum cleaning efficiency, has side brushes to remove dust from corners and curves, and has a front opening to pick up the big bits. Each stroke will deliver an immediate clean result.

Specifications

Design

Colour: Greige

Filtration

Dust bag type: s-bag

Dust capacity: 4 l

Exhaust filter: Ultra Clean Air HEPA 13 washable filter

HEPA AirSeal

Nozzles and accessories

Accessories: Crevice tool, Small nozzle

Accessory storage: On handgrip

Additional nozzle: Super Parquet nozzle

Standard nozzle: TriActive nozzle

Performance

Airflow (max): 39 l/s

Input power (IEC): 1250 W

Input power (max): 1250 W

Noise level (Lc IEC): 76 dB

Suction power (max): 375 W

Vacuum (max): 28 kPa

Usability

Action radius: 12 m

Carrying handle: Top and front

Clean Comfort cassette

Cord length: 9 m

Tube coupling: Button

Dust bag full indicator

Tube type: Metal lacquered 2-piece telescopic tube

Wheel type: Rubber

Weight and dimensions

Weight of product: 6.5 kg

