

PHILIPS

Vacuum cleaner
with bag

Performer

1250W (EnergyCare)

375W suction power

HEPA 13 washable filter

Parquet

FC9178/03



Greener every day

Save 35% energy with highly efficient HD motor*

The highest suction power ever, resulting in effortless cleaning: this is what the Philips Performer vacuum cleaner FC9178/03 is all about. The new highly efficient HD motor uses up to 35% less energy, while keeping the suction power.

Low power consumption, high-power results

- New 1250 Watt HD motor generates max. 375 Watt suction power

Less waste in the environment

- At least 60% of plastics is sustainable

Highly efficient anti-allergy system

- HEPA AirSeal plus HEPA 13 filter
- ECARF Seal of Quality for trusted results

Superior results on all floors

- Test winning multi-nozzle for thorough & gentle cleaning

Superior hard-floor cleaning

- Super Parquet nozzle removes 3 x more sticky dirt




asimpleswitch.com



asimpleswitch.com

Highlights

New 1250 Watt HD motor



Highly efficient 1250 Watt HD (High Density) motor generates 375 Watt max. suction power, which means that you use 35% less energy without giving in on the cleaning result.

HEPA AirSeal, HEPA 13 filter



This Philips vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

Multi nozzle



Superior cleaning on all floor types thanks to this consumer test winning multi-nozzle. Its wide air channel is designed for optimal airflow, providing effective cleaning even alongside walls. Its special double hinge ensures permanent contact with the floor for best cleaning results. Designed and produced in Germany by WesselWerk, this high quality nozzle has a metal soleplate with surrounding brushes that gently and thoroughly clean hard floors, crevices and carpets.

Super Parquet nozzle



The Super Parquet nozzle allows you really clean hard floors of all kinds in one go, without the risk of harming them. Using the absorption capacity of the micro-fibre pads, together with the suction power of the vacuum cleaner, you achieve maximum result without requiring any detergents or brushes.

Specifications

Design

Color: Greige

Filtration

Dust bag type: s-bag
Exhaust filter: Ultra Clean Air HEPA 13 washable filter
Dust capacity: 4 L
HEPA Air Seal

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle
Accessory storage: On handgrip
Additional nozzle: Super Parquet nozzle
Standard nozzle: Multi nozzle

Performance

Airflow (max): 39 l/s
Input power (IEC): 1250 W
Input power (max): 1250 W
Noise level (Lc IEC): 78 dB
Suction power (max): 375 W
Vacuum (max): 28 kPa

Usability

Carrying handle: Top and front
Clean Comfort cassette
Tube coupling: Button
Dust full indicator
Tube type: Metal lacquered 2-piece telescopic tube
Wheel type: Rubber
Action radius: 12 m
Cord length: 7 m

Weight and dimensions

Weight of product: 6.5 kg
Dimensions of product (LxWxH): 500 x 320 x 280 mm



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

